

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286514

Luminaire Tested: P3AS05R409030D2WDE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286514
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R409030D2WDE010 E3DLP1WH
Description: 3in Adjustable Dim to Warm LED luminaire with, R40 optic, 3000K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 582.0 lumens
Efficiency: N/A
Efficacy: 52.4 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286514

CATALOG NUMBER: P3AS05R409030D2WDE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1286514

CATALOG NUMBER: P3AS05R409030D2WDE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	99	94	91	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86
5	96	88	83	79	94	88	83	79	86	82	78		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	68	84	76	71	67	75	70	67		74	70	67		73
9	82	73	68	64	81	73	68	64	72	67	64		71	67	64		70
10	78	70	65	62	78	70	65	61	69	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	257523
5°	250054
10°	226916
15°	187470
20°	135228
25°	83642
30°	45273
35°	23396
40°	12738
45°	7133
50°	3582
55°	2676
60°	2412
65°	2335
70°	2244
75°	2118
80°	1894
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7133 cd/sqm

TEST NUMBER: P1286514

CATALOG NUMBER: P3AS05R409030D2WDE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.7	18.0
10°-20°	224.9	38.6
20°-30°	160.5	27.6
30°-40°	59.1	10.1
40°-50°	18.6	3.2
50°-60°	6.5	1.1
60°-70°	4.5	0.8
70°-80°	2.6	0.5
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	490.0	84.2
0°-40°	549.1	94.3
0°-60°	574.2	98.7
0°-90°	582.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	582.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1174	
5°	1136	105
15°	826	225
25°	346	160
35°	87	59
45°	23	19
55°	7	6
65°	4	4
75°	2	3
85°	0	1
90°	0	

TEST NUMBER: P1286514

CATALOG NUMBER: P3AS05R409030D2WDE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1174.4
2.5°	1165.4
5°	1136.0
7.5°	1087.0
10°	1019.1
12.5°	932.7
15°	825.8
17.5°	705.9
20°	579.5
22.5°	455.1
25°	345.7
27.5°	253.8
30°	178.8
32.5°	125.4
35°	87.4
37.5°	61.9
40°	44.5
42.5°	32.0
45°	23.0
47.5°	15.5
50°	10.5
52.5°	7.5
55°	7.0
57.5°	6.5
60°	5.5
62.5°	5.0
65°	4.5
67.5°	4.0
70°	3.5
72.5°	3.0
75°	2.5
77.5°	2.0
80°	1.5
82.5°	1.0
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)