

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285752

Luminaire Tested: P3AS13R65B2750DE010 E3D1H_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285752
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R65B2750DE010 E3D1H_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R65 optic, 2700K CCT AND, 90CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 915.0 lumens
Efficiency: N/A
Efficacy: 47.9 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285752

CATALOG NUMBER: P3AS13R65B2750DE010 E3D1H_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1285752

CATALOG NUMBER: P3AS13R65B2750DE010 E3D1H_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	86	83	82
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84	81	78	77
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	70	65	83	75	69	65	73	69	65		72	68	65		71	67	64	63
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67	63	60	59
9	77	67	61	58	76	67	61	57	66	61	57		65	60	57		64	60	57	56
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61	57	54	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	245178
5°	227646
10°	220147
15°	212169
20°	196157
25°	178704
30°	138072
35°	80040
40°	31745
45°	13521
50°	3207
55°	421
60°	351
65°	208
70°	256
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13521 cd/sqm

TEST NUMBER: P1285752

CATALOG NUMBER: P3AS13R65B2750DE010 E3D1H_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.5	10.7
10°-20°	260.4	28.5
20°-30°	329.6	36.0
30°-40°	187.7	20.5
40°-50°	37.3	4.1
50°-60°	1.9	0.2
60°-70°	0.5	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	687.5	75.1
0°-40°	875.2	95.6
0°-60°	914.4	99.9
0°-90°	915.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	915.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1118	
5°	1034	98
15°	935	260
25°	739	330
35°	299	188
45°	44	37
55°	1	2
65°	0	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1285752

CATALOG NUMBER: P3AS13R65B2750DE010 E3D1H_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1118.1
1°	1109.8
2°	1091.8
3°	1070.7
4°	1050.0
5°	1034.2
6°	1022.6
7°	1013.2
8°	1004.9
9°	996.6
10°	988.7
11°	980.1
12°	971.1
13°	960.2
14°	948.5
15°	934.6
16°	918.0
17°	900.0
18°	880.4
19°	859.7
20°	840.6
21°	821.0
22°	803.3
23°	784.9
24°	763.5
25°	738.6
26°	708.9
27°	673.2
28°	633.0
29°	590.1
30°	545.3
31°	496.1
32°	447.2
32.5°	422.0
33°	397.5
34°	347.9
35°	299.0
36°	253.9
37°	209.1
37.5°	186.2
38°	167.7
39°	135.8
40°	110.9
42.5°	68.4
45°	43.6



TEST NUMBER: P1285752

CATALOG NUMBER: P3AS13R65B2750DE010 E3D1H_2700K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	25.6
50°	9.4
52.5°	1.9
55°	1.1
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)