

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285807

Luminaire Tested: P3AS13R65B2750DE010 E3DLD1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285807
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R65B2750DE010 E3DLD1GPH_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R65 optic, 2700K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 296.0 lumens
Efficiency: N/A
Efficacy: 15.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285807

CATALOG NUMBER: P3AS13R65B2750DE010 E3DLD1GPH_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1285807

CATALOG NUMBER: P3AS13R65B2750DE010 E3DLD1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	52671
5°	51970
10°	50233
15°	47356
20°	43684
25°	39656
30°	35119
35°	29874
40°	23787
45°	16777
50°	9757
55°	5314
60°	4956
65°	4462
70°	4103
75°	3813
80°	3283
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16777 cd/sqm

TEST NUMBER: P1285807

CATALOG NUMBER: P3AS13R65B2750DE010 E3DLD1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.2	7.5
10°-20°	58.4	19.7
20°-30°	75.0	25.3
30°-40°	69.4	23.4
40°-50°	41.9	14.2
50°-60°	14.3	4.8
60°-70°	8.6	2.9
70°-80°	4.9	1.6
80°-90°	1.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	155.6	52.6
0°-40°	225.0	76.0
0°-60°	281.1	95.0
0°-90°	296.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	296.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	240	
5°	236	22
15°	209	58
25°	164	75
35°	112	69
45°	54	42
55°	14	14
65°	9	9
75°	4	5
85°	1	1
90°	0	

TEST NUMBER: P1285807

CATALOG NUMBER: P3AS13R65B2750DE010 E3DLD1GPH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	240.2
2.5°	239.1
5°	236.1
7.5°	231.6
10°	225.6
12.5°	218.0
15°	208.6
17.5°	198.5
20°	187.2
22.5°	175.6
25°	163.9
27.5°	151.5
30°	138.7
32.5°	125.9
35°	111.6
37.5°	97.7
40°	83.1
42.5°	68.4
45°	54.1
47.5°	41.0
50°	28.6
52.5°	18.0
55°	13.9
57.5°	12.4
60°	11.3
62.5°	9.8
65°	8.6
67.5°	7.5
70°	6.4
72.5°	5.6
75°	4.5
77.5°	3.8
80°	2.6
82.5°	1.9
85°	1.1
87.5°	0.8
90°	0.0

(END OF REPORT)