

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286567

Luminaire Tested: P3AS05R509030D2WDE010 E3DLP1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1286567  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R509030D2WDE010 E3DLP1MW  
Description: 3in Adjustable Dim to Warm LED luminaire with, R50 optic, 3000K CCT AND, 90CRI ,  
E3DLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 369.0 lumens  
Efficiency: N/A  
Efficacy: 33.2 lumens/watt  
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1286567  
CATALOG NUMBER: P3AS05R509030D2WDE010 E3DLP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1286567  
 CATALOG NUMBER: P3AS05R509030D2WDE010 E3DLP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79				79
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73				73
5	91	83	76	72	90	82	76	72	80	75	71	78	74	70	77	73	70	68				68
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64				64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60				60
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56				56
9	75	65	59	55	74	64	59	55	63	58	55	63	58	54	62	57	54	53				53
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50				50

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	107316
5°	104424
10°	96302
15°	84700
20°	70846
25°	56181
30°	41222
35°	28349
40°	18005
45°	10079
50°	5458
55°	4588
60°	3947
65°	3632
70°	3206
75°	2965
80°	2526
85°	2516

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10079 cd/sqm



TEST NUMBER: P1286567

CATALOG NUMBER: P3AS05R509030D2WDE010 E3DLP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.0	11.9
10°-20°	103.3	28.0
20°-30°	105.7	28.6
30°-40°	67.0	18.2
40°-50°	26.7	7.2
50°-60°	10.8	2.9
60°-70°	6.9	1.9
70°-80°	3.6	1.0
80°-90°	1.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	253.0	68.5
0°-40°	320.0	86.7
0°-60°	357.4	96.9
0°-90°	369.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	369.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	489	
5°	474	44
15°	373	103
25°	232	106
35°	106	67
45°	32	27
55°	12	11
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1286567  
CATALOG NUMBER: P3AS05R509030D2WDE010 E3DLP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	489.4
2.5°	485.9
5°	474.4
7.5°	456.5
10°	432.5
12.5°	404.0
15°	373.1
17.5°	339.1
20°	303.6
22.5°	268.2
25°	232.2
27.5°	196.3
30°	162.8
32.5°	132.8
35°	105.9
37.5°	82.9
40°	62.9
42.5°	46.4
45°	32.5
47.5°	22.0
50°	16.0
52.5°	13.5
55°	12.0
57.5°	10.5
60°	9.0
62.5°	8.0
65°	7.0
67.5°	6.0
70°	5.0
72.5°	4.0
75°	3.5
77.5°	2.5
80°	2.0
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)