

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286568

Luminaire Tested: P3AS05R509030D2WDE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286568
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R509030D2WDE010 E3DLP1WH
Description: 3in Adjustable Dim to Warm LED luminaire with, R50 optic, 3000K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 562.0 lumens
Efficiency: N/A
Efficacy: 50.6 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286568
CATALOG NUMBER: P3AS05R509030D2WDE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1286568
 CATALOG NUMBER: P3AS05R509030D2WDE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94	94	94	94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87	87	87	87
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82	82	82	82
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78	76	76	76	76
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72	72	72	72
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69	67	67	67	67
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64	64	64	64
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60	60	60	60
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58	57	57	57	57
10	74	65	59	56	73	65	59	56	64	59	55	63	58	55	62	58	55	54	54	54	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	178933
5°	175324
10°	164214
15°	147016
20°	123724
25°	94433
30°	61351
35°	36379
40°	21039
45°	10544
50°	3923
55°	3058
60°	2851
65°	2594
70°	2565
75°	2542
80°	2526
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10544 cd/sqm



TEST NUMBER: P1286568

CATALOG NUMBER: P3AS05R509030D2WDE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.1	13.2
10°-20°	179.1	31.9
20°-30°	175.7	31.3
30°-40°	88.5	15.7
40°-50°	28.0	5.0
50°-60°	7.3	1.3
60°-70°	5.1	0.9
70°-80°	3.2	0.6
80°-90°	1.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	428.9	76.3
0°-40°	517.4	92.1
0°-60°	552.6	98.3
0°-90°	562.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	562.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	816	
5°	796	74
15°	648	179
25°	390	176
35°	136	89
45°	34	28
55°	8	7
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1286568
CATALOG NUMBER: P3AS05R509030D2WDE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	816.0
2.5°	811.0
5°	796.5
7.5°	770.5
10°	737.5
12.5°	695.1
15°	647.6
17.5°	592.6
20°	530.2
22.5°	462.7
25°	390.3
27.5°	313.3
30°	242.3
32.5°	182.4
35°	135.9
37.5°	100.4
40°	73.5
42.5°	52.0
45°	34.0
47.5°	19.5
50°	11.5
52.5°	8.5
55°	8.0
57.5°	7.0
60°	6.5
62.5°	6.0
65°	5.0
67.5°	4.5
70°	4.0
72.5°	3.5
75°	3.0
77.5°	2.5
80°	2.0
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)