

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285832

Luminaire Tested: P3AS13R65B2750DE010 E3DLD1WMH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285832
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R65B2750DE010 E3DLD1WMH_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R65 optic, 2700K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 603.9 lumens
Efficiency: N/A
Efficacy: 31.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285832

CATALOG NUMBER: P3AS13R65B2750DE010 E3DLD1WMH_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1285832

CATALOG NUMBER: P3AS13R65B2750DE010 E3DLD1WMH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91											
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82											
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74											
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67											
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61											
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56											
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51											
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47											
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44											
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	107491
5°	106031
10°	102492
15°	96641
20°	89141
25°	80908
30°	71682
35°	60980
40°	48519
45°	34267
50°	19888
55°	10857
60°	10087
65°	9132
70°	8335
75°	7795
80°	6819
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 34267 cd/sqm

TEST NUMBER: P1285832

CATALOG NUMBER: P3AS13R65B2750DE010 E3DLD1WMH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.3	7.5
10°-20°	119.1	19.7
20°-30°	153.1	25.3
30°-40°	141.6	23.4
40°-50°	85.5	14.2
50°-60°	29.2	4.8
60°-70°	17.5	2.9
70°-80°	9.9	1.6
80°-90°	2.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	317.5	52.6
0°-40°	459.1	76.0
0°-60°	573.7	95.0
0°-90°	603.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	603.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	490	
5°	482	45
15°	426	119
25°	334	153
35°	228	142
45°	110	85
55°	28	29
65°	18	18
75°	9	10
85°	2	3
90°	0	

TEST NUMBER: P1285832

CATALOG NUMBER: P3AS13R65B2750DE010 E3DLD1WMH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	490.2
2.5°	487.9
5°	481.7
7.5°	472.5
10°	460.3
12.5°	444.9
15°	425.7
17.5°	405.0
20°	382.0
22.5°	358.2
25°	334.4
27.5°	309.1
30°	283.1
32.5°	257.0
35°	227.8
37.5°	199.4
40°	169.5
42.5°	139.6
45°	110.5
47.5°	83.6
50°	58.3
52.5°	36.8
55°	28.4
57.5°	25.3
60°	23.0
62.5°	19.9
65°	17.6
67.5°	15.3
70°	13.0
72.5°	11.5
75°	9.2
77.5°	7.7
80°	5.4
82.5°	3.8
85°	2.3
87.5°	1.5
90°	0.0

(END OF REPORT)