

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286583

Luminaire Tested: P3AS05R559030D2WDE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286583
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R559030D2WDE010 E3DL1LI
Description: 3in Adjustable Dim to Warm LED luminaire with, R55 optic, 3000K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 544.0 lumens
Efficiency: N/A
Efficacy: 49.0 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286583

CATALOG NUMBER: P3AS05R559030D2WDE010 E3DL1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1286583

CATALOG NUMBER: P3AS05R559030D2WDE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87		
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	85	82	81		
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	82	79	77	75		
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70		
6	88	79	73	69	86	78	73	68	77	72	68	75	71	68	74	70	67	66		
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62		
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58		
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55		
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	149374
5°	147853
10°	142794
15°	131987
20°	113900
25°	89957
30°	63807
35°	41144
40°	24703
45°	13924
50°	7505
55°	2676
60°	2412
65°	2335
70°	2244
75°	2118
80°	1894
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 13924 cd/sqm

TEST NUMBER: P1286583

CATALOG NUMBER: P3AS05R559030D2WDE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.2	11.6
10°-20°	160.8	29.6
20°-30°	168.5	31.0
30°-40°	98.3	18.1
40°-50°	36.8	6.8
50°-60°	8.7	1.6
60°-70°	4.5	0.8
70°-80°	2.6	0.5
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	392.4	72.1
0°-40°	490.7	90.2
0°-60°	536.2	98.6
0°-90°	544.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	544.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	681	
5°	672	63
15°	581	161
25°	372	168
35°	154	98
45°	45	37
55°	7	9
65°	4	4
75°	2	3
85°	0	1
90°	0	

TEST NUMBER: P1286583

CATALOG NUMBER: P3AS05R559030D2WDE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	681.2
2.5°	679.2
5°	671.7
7.5°	659.8
10°	641.3
12.5°	615.3
15°	581.4
17.5°	538.5
20°	488.1
22.5°	431.7
25°	371.8
27.5°	310.4
30°	252.0
32.5°	199.1
35°	153.7
37.5°	116.8
40°	86.3
42.5°	61.9
45°	44.9
47.5°	32.4
50°	22.0
52.5°	12.5
55°	7.0
57.5°	6.0
60°	5.5
62.5°	5.0
65°	4.5
67.5°	4.0
70°	3.5
72.5°	3.0
75°	2.5
77.5°	2.0
80°	1.5
82.5°	1.0
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)