

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285836

Luminaire Tested: P3AS13R65B2750DE010 E3DLD1WMH\_5000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1285836  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R65B2750DE010 E3DLD1WMH\_5000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R65 optic, 5000K CCT AND, 80CRI , E3DLD1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 647.0 lumens  
Efficiency: N/A  
Efficacy: 33.9 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 19.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1285836

CATALOG NUMBER: P3AS13R65B2750DE010 E3DLD1WMH\_5000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1285836

CATALOG NUMBER: P3AS13R65B2750DE010 E3DLD1WMH\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |  |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |     |     |  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |  | 100 |
| 1   | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 101 | 102 | 100 | 98  |  | 99  | 97  | 95  |  | 95  | 94  | 93  |  | 91  |
| 2   | 105 | 99  | 94  | 90  | 103 | 97  | 93  | 89  | 94  | 90  | 87  |  | 91  | 88  | 85  |  | 88  | 86  | 84  |  | 82  |
| 3   | 99  | 91  | 85  | 80  | 96  | 89  | 84  | 79  | 87  | 82  | 78  |  | 84  | 80  | 77  |  | 82  | 78  | 76  |  | 74  |
| 4   | 92  | 83  | 77  | 72  | 90  | 82  | 76  | 71  | 80  | 75  | 70  |  | 78  | 73  | 70  |  | 76  | 72  | 69  |  | 67  |
| 5   | 87  | 77  | 70  | 65  | 85  | 76  | 69  | 65  | 74  | 68  | 64  |  | 72  | 67  | 63  |  | 71  | 66  | 63  |  | 61  |
| 6   | 82  | 71  | 64  | 59  | 80  | 70  | 64  | 59  | 69  | 63  | 58  |  | 67  | 62  | 58  |  | 66  | 61  | 58  |  | 56  |
| 7   | 77  | 66  | 59  | 54  | 75  | 65  | 59  | 54  | 64  | 58  | 54  |  | 63  | 57  | 53  |  | 61  | 57  | 53  |  | 51  |
| 8   | 72  | 61  | 55  | 50  | 71  | 61  | 54  | 50  | 60  | 54  | 49  |  | 59  | 53  | 49  |  | 58  | 53  | 49  |  | 47  |
| 9   | 68  | 57  | 51  | 46  | 67  | 57  | 50  | 46  | 56  | 50  | 46  |  | 55  | 49  | 46  |  | 54  | 49  | 45  |  | 44  |
| 10  | 65  | 54  | 47  | 43  | 64  | 53  | 47  | 43  | 52  | 47  | 43  |  | 52  | 46  | 42  |  | 51  | 46  | 42  |  | 41  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 115144 |
| 5°  | 113581 |
| 10° | 109773 |
| 15° | 103519 |
| 20° | 95488  |
| 25° | 86690  |
| 30° | 76771  |
| 35° | 65317  |
| 40° | 51983  |
| 45° | 36686  |
| 50° | 21287  |
| 55° | 11622  |
| 60° | 10832  |
| 65° | 9806   |
| 70° | 8976   |
| 75° | 8388   |
| 80° | 7324   |
| 85° | 6290   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 36686 cd/sqm

TEST NUMBER: P1285836

CATALOG NUMBER: P3AS13R65B2750DE010 E3DLD1WMH\_5000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 48.5   | 7.5       |
| 10°-20°   | 127.6  | 19.7      |
| 20°-30°   | 164.0  | 25.3      |
| 30°-40°   | 151.7  | 23.4      |
| 40°-50°   | 91.6   | 14.2      |
| 50°-60°   | 31.2   | 4.8       |
| 60°-70°   | 18.8   | 2.9       |
| 70°-80°   | 10.6   | 1.6       |
| 80°-90°   | 3.0    | 0.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 340.1  | 52.6      |
| 0°-40°    | 491.8  | 76.0      |
| 0°-60°    | 614.5  | 95.0      |
| 0°-90°    | 647.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 647.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 525 |      |
| 5°  | 516 | 49   |
| 15° | 456 | 128  |
| 25° | 358 | 164  |
| 35° | 244 | 152  |
| 45° | 118 | 92   |
| 55° | 30  | 31   |
| 65° | 19  | 19   |
| 75° | 10  | 11   |
| 85° | 2   | 3    |
| 90° | 0   |      |

TEST NUMBER: P1285836

CATALOG NUMBER: P3AS13R65B2750DE010 E3DLD1WMH\_5000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 525.1 |
| 2.5°  | 522.6 |
| 5°    | 516.0 |
| 7.5°  | 506.2 |
| 10°   | 493.0 |
| 12.5° | 476.6 |
| 15°   | 456.0 |
| 17.5° | 433.9 |
| 20°   | 409.2 |
| 22.5° | 383.7 |
| 25°   | 358.3 |
| 27.5° | 331.1 |
| 30°   | 303.2 |
| 32.5° | 275.3 |
| 35°   | 244.0 |
| 37.5° | 213.6 |
| 40°   | 181.6 |
| 42.5° | 149.5 |
| 45°   | 118.3 |
| 47.5° | 89.6  |
| 50°   | 62.4  |
| 52.5° | 39.4  |
| 55°   | 30.4  |
| 57.5° | 27.1  |
| 60°   | 24.7  |
| 62.5° | 21.4  |
| 65°   | 18.9  |
| 67.5° | 16.4  |
| 70°   | 14.0  |
| 72.5° | 12.3  |
| 75°   | 9.9   |
| 77.5° | 8.2   |
| 80°   | 5.8   |
| 82.5° | 4.1   |
| 85°   | 2.5   |
| 87.5° | 1.6   |
| 90°   | 0.0   |

(END OF REPORT)