

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286601

Luminaire Tested: P3AS05R609030D2WDE010 E3CB1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1286601  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R609030D2WDE010 E3CB1MW  
Description: 3in Adjustable Dim to Warm LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3CB1M  
TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 645.0 lumens  
Efficiency: N/A  
Efficacy: 58.1 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1286601  
CATALOG NUMBER: P3AS05R609030D2WDE010 E3CB1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1286601  
 CATALOG NUMBER: P3AS05R609030D2WDE010 E3CB1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1   | 114 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 105 | 103 | 101 | 101 | 100 | 98  | 97  | 96  | 95  | 94  | 94  | 94  | 94  |
| 2   | 108 | 103 | 99  | 96  | 106 | 102 | 98  | 95  | 98  | 95  | 93  | 95  | 93  | 91  | 93  | 91  | 89  | 87  | 87  | 87  | 87  |
| 3   | 103 | 96  | 91  | 88  | 101 | 95  | 90  | 87  | 92  | 89  | 85  | 90  | 87  | 84  | 88  | 85  | 83  | 81  | 81  | 81  | 81  |
| 4   | 98  | 90  | 85  | 81  | 96  | 89  | 84  | 80  | 87  | 83  | 79  | 85  | 81  | 78  | 83  | 80  | 77  | 76  | 76  | 76  | 76  |
| 5   | 93  | 84  | 79  | 74  | 91  | 84  | 78  | 74  | 82  | 77  | 73  | 80  | 76  | 73  | 79  | 75  | 72  | 71  | 71  | 71  | 71  |
| 6   | 88  | 79  | 73  | 69  | 87  | 79  | 73  | 69  | 77  | 72  | 68  | 76  | 71  | 68  | 74  | 70  | 68  | 66  | 66  | 66  | 66  |
| 7   | 84  | 75  | 69  | 64  | 82  | 74  | 68  | 64  | 73  | 68  | 64  | 71  | 67  | 64  | 70  | 66  | 63  | 62  | 62  | 62  | 62  |
| 8   | 80  | 70  | 64  | 60  | 78  | 70  | 64  | 60  | 69  | 64  | 60  | 68  | 63  | 60  | 67  | 62  | 59  | 58  | 58  | 58  | 58  |
| 9   | 76  | 66  | 61  | 57  | 75  | 66  | 60  | 56  | 65  | 60  | 56  | 64  | 59  | 56  | 63  | 59  | 56  | 55  | 55  | 55  | 55  |
| 10  | 72  | 63  | 57  | 53  | 71  | 62  | 57  | 53  | 62  | 56  | 53  | 61  | 56  | 53  | 60  | 56  | 53  | 51  | 51  | 51  | 51  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 154023 |
| 5°  | 147919 |
| 10° | 152280 |
| 15° | 154257 |
| 20° | 136209 |
| 25° | 114781 |
| 30° | 93103  |
| 35° | 60632  |
| 40° | 27852  |
| 45° | 10668  |
| 50° | 3582   |
| 55° | 956    |
| 60° | 877    |
| 65° | 778    |
| 70° | 641    |
| 75° | 847    |
| 80° | 631    |
| 85° | 1258   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10668 cd/sqm



TEST NUMBER: P1286601  
 CATALOG NUMBER: P3AS05R609030D2WDE010 E3CB1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 64.7   | 10.0      |
| 10°-20°   | 186.1  | 28.8      |
| 20°-30°   | 217.0  | 33.6      |
| 30°-40°   | 140.0  | 21.7      |
| 40°-50°   | 31.4   | 4.9       |
| 50°-60°   | 3.1    | 0.5       |
| 60°-70°   | 1.5    | 0.2       |
| 70°-80°   | 0.9    | 0.1       |
| 80°-90°   | 0.3    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 467.8  | 72.5      |
| 0°-40°    | 607.8  | 94.2      |
| 0°-60°    | 642.3  | 99.6      |
| 0°-90°    | 645.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 645.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 702 |      |
| 5°  | 672 | 65   |
| 15° | 680 | 186  |
| 25° | 474 | 217  |
| 35° | 226 | 140  |
| 45° | 34  | 31   |
| 55° | 2   | 3    |
| 65° | 2   | 1    |
| 75° | 1   | 1    |
| 85° | 0   | 0    |
| 90° | 0   |      |



TEST NUMBER: P1286601  
CATALOG NUMBER: P3AS05R609030D2WDE010 E3CB1MW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 702.4 |
| 2.5°  | 690.9 |
| 5°    | 672.0 |
| 7.5°  | 671.0 |
| 10°   | 683.9 |
| 12.5° | 692.4 |
| 15°   | 679.5 |
| 17.5° | 640.5 |
| 20°   | 583.7 |
| 22.5° | 524.3 |
| 25°   | 474.4 |
| 27.5° | 425.5 |
| 30°   | 367.7 |
| 32.5° | 299.8 |
| 35°   | 226.5 |
| 37.5° | 154.6 |
| 40°   | 97.3  |
| 42.5° | 58.4  |
| 45°   | 34.4  |
| 47.5° | 20.0  |
| 50°   | 10.5  |
| 52.5° | 3.5   |
| 55°   | 2.5   |
| 57.5° | 2.0   |
| 60°   | 2.0   |
| 62.5° | 1.5   |
| 65°   | 1.5   |
| 67.5° | 1.5   |
| 70°   | 1.0   |
| 72.5° | 1.0   |
| 75°   | 1.0   |
| 77.5° | 0.5   |
| 80°   | 0.5   |
| 82.5° | 0.5   |
| 85°   | 0.5   |
| 87.5° | 0.0   |
| 90°   | 0.0   |

(END OF REPORT)