

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286611

Luminaire Tested: P3AS05R609030D2WDE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286611
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609030D2WDE010 E3DL1H
Description: 3in Adjustable Dim to Warm LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 525.0 lumens
Efficiency: N/A
Efficacy: 47.3 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286611
CATALOG NUMBER: P3AS05R609030D2WDE010 E3DL1H

Luminous Intensity Polar Plot





TEST NUMBER: P1286611
 CATALOG NUMBER: P3AS05R609030D2WDE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.5	10.0
10°-20°	136.5	26.0
20°-30°	155.6	29.6
30°-40°	110.3	21.0
40°-50°	50.1	9.5
50°-60°	10.6	2.0
60°-70°	5.1	1.0
70°-80°	3.2	0.6
80°-90°	1.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	344.6	65.6
0°-40°	454.9	86.7
0°-60°	515.6	98.2
0°-90°	525.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	525.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	565	
5°	558	53
15°	492	137
25°	342	156
35°	176	110
45°	63	50
55°	8	11
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1286611

CATALOG NUMBER: P3AS05R609030D2WDE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	565.3
2.5°	563.4
5°	557.9
7.5°	548.4
10°	535.4
12.5°	516.9
15°	492.0
17.5°	460.6
20°	423.6
22.5°	383.7
25°	341.8
27.5°	298.9
30°	256.0
32.5°	215.1
35°	175.6
37.5°	140.7
40°	109.3
42.5°	82.8
45°	62.9
47.5°	46.9
50°	30.9
52.5°	14.5
55°	8.0
57.5°	7.0
60°	6.5
62.5°	6.0
65°	5.0
67.5°	4.5
70°	4.0
72.5°	3.5
75°	3.0
77.5°	2.5
80°	2.0
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)