

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285923

Luminaire Tested: P3AS13R70B2750DE010 E3DL1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285923
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R70B2750DE010 E3DL1GPH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R70 optic, 3000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 373.0 lumens
Efficiency: N/A
Efficacy: 19.5 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285923

CATALOG NUMBER: P3AS13R70B2750DE010 E3DL1GPH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1285923

CATALOG NUMBER: P3AS13R70B2750DE010 E3DL1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	53	74	64	58	53	63	57	53		62	57	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	49	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	72209
5°	71340
10°	69293
15°	66357
20°	62142
25°	56471
30°	48767
35°	38869
40°	28310
45°	18607
50°	8733
55°	2676
60°	2588
65°	2491
70°	2372
75°	2542
80°	2399
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18607 cd/sqm

TEST NUMBER: P1285923

CATALOG NUMBER: P3AS13R70B2750DE010 E3DL1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.5	8.2
10°-20°	81.8	21.9
20°-30°	106.3	28.5
30°-40°	90.2	24.2
40°-50°	46.5	12.5
50°-60°	9.0	2.4
60°-70°	4.8	1.3
70°-80°	3.0	0.8
80°-90°	0.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	218.6	58.6
0°-40°	308.8	82.8
0°-60°	364.3	97.7
0°-90°	373.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	373.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	329	
5°	324	31
15°	292	82
25°	233	106
35°	145	90
45°	60	47
55°	7	9
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1285923

CATALOG NUMBER: P3AS13R70B2750DE010 E3DL1GPH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	329.3
2.5°	328.2
5°	324.1
7.5°	318.2
10°	311.2
12.5°	302.3
15°	292.3
17.5°	280.0
20°	266.3
22.5°	250.8
25°	233.4
27.5°	213.7
30°	192.6
32.5°	169.3
35°	145.2
37.5°	121.5
40°	98.9
42.5°	77.8
45°	60.0
47.5°	44.1
50°	25.6
52.5°	11.1
55°	7.0
57.5°	6.7
60°	5.9
62.5°	5.6
65°	4.8
67.5°	4.4
70°	3.7
72.5°	3.3
75°	3.0
77.5°	2.2
80°	1.9
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)