

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286668

Luminaire Tested: P3AS05R709030D2WDE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286668
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709030D2WDE010 E3DL1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R70 optic, 3000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 246.0 lumens
Efficiency: N/A
Efficacy: 22.2 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286668

CATALOG NUMBER: P3AS05R709030D2WDE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1286668

CATALOG NUMBER: P3AS05R709030D2WDE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	53	74	64	58	53	63	57	53		62	57	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	49	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47628
5°	47061
10°	45691
15°	43769
20°	40977
25°	37236
30°	32157
35°	25645
40°	18664
45°	12280
50°	5765
55°	1759
60°	1710
65°	1660
70°	1539
75°	1694
80°	1515
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12280 cd/sqm

TEST NUMBER: P1286668

CATALOG NUMBER: P3AS05R709030D2WDE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.1	8.2
10°-20°	53.9	21.9
20°-30°	70.1	28.5
30°-40°	59.5	24.2
40°-50°	30.7	12.5
50°-60°	5.9	2.4
60°-70°	3.2	1.3
70°-80°	2.0	0.8
80°-90°	0.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	144.2	58.6
0°-40°	203.7	82.8
0°-60°	240.3	97.7
0°-90°	246.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	246.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	217	
5°	214	20
15°	193	54
25°	154	70
35°	96	59
45°	40	31
55°	5	6
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1286668

CATALOG NUMBER: P3AS05R709030D2WDE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	217.2
2.5°	216.4
5°	213.8
7.5°	209.9
10°	205.2
12.5°	199.3
15°	192.8
17.5°	184.7
20°	175.6
22.5°	165.4
25°	153.9
27.5°	141.0
30°	127.0
32.5°	111.6
35°	95.8
37.5°	80.1
40°	65.2
42.5°	51.3
45°	39.6
47.5°	29.1
50°	16.9
52.5°	7.3
55°	4.6
57.5°	4.4
60°	3.9
62.5°	3.7
65°	3.2
67.5°	2.9
70°	2.4
72.5°	2.2
75°	2.0
77.5°	1.5
80°	1.2
82.5°	0.7
85°	0.5
87.5°	0.2
90°	0.0

(END OF REPORT)