

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285950

Luminaire Tested: P3AS13R70B2750DE010 E3DL1WMH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285950
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R70B2750DE010 E3DL1WMH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R70 optic, 4000K CCT AND, 80CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 775.0 lumens
Efficiency: N/A
Efficacy: 40.6 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285950

CATALOG NUMBER: P3AS13R70B2750DE010 E3DL1WMH_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1285950

CATALOG NUMBER: P3AS13R70B2750DE010 E3DL1WMH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	53	74	64	58	53	63	57	53		62	57	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	49	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	150032
5°	148228
10°	143952
15°	137844
20°	129138
25°	117321
30°	101332
35°	80763
40°	58824
45°	38671
50°	18115
55°	5582
60°	5394
65°	5189
70°	4937
75°	5253
80°	4799
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 38671 cd/sqm

TEST NUMBER: P1285950

CATALOG NUMBER: P3AS13R70B2750DE010 E3DL1WMH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.4	8.2
10°-20°	169.9	21.9
20°-30°	220.9	28.5
30°-40°	187.4	24.2
40°-50°	96.6	12.5
50°-60°	18.6	2.4
60°-70°	10.1	1.3
70°-80°	6.2	0.8
80°-90°	1.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	454.2	58.6
0°-40°	641.7	82.8
0°-60°	756.9	97.7
0°-90°	775.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	775.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	684	
5°	673	63
15°	607	170
25°	485	221
35°	302	187
45°	125	97
55°	15	19
65°	10	10
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1285950

CATALOG NUMBER: P3AS13R70B2750DE010 E3DL1WMH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	684.2
2.5°	681.9
5°	673.4
7.5°	661.1
10°	646.5
12.5°	628.0
15°	607.2
17.5°	581.8
20°	553.4
22.5°	521.0
25°	484.9
27.5°	444.1
30°	400.2
32.5°	351.7
35°	301.7
37.5°	252.4
40°	205.5
42.5°	161.6
45°	124.7
47.5°	91.6
50°	53.1
52.5°	23.1
55°	14.6
57.5°	13.9
60°	12.3
62.5°	11.5
65°	10.0
67.5°	9.2
70°	7.7
72.5°	6.9
75°	6.2
77.5°	4.6
80°	3.8
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)