

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286674

Luminaire Tested: P3AS05R709030D2WDE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286674
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709030D2WDE010 E3DLP1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R70 optic, 3000K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 175.9 lumens
Efficiency: N/A
Efficacy: 15.9 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286674

CATALOG NUMBER: P3AS05R709030D2WDE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1286674

CATALOG NUMBER: P3AS05R709030D2WDE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	41291
5°	40524
10°	38209
15°	34688
20°	30336
25°	25598
30°	20940
35°	16249
40°	11622
45°	7350
50°	3684
55°	2256
60°	1930
65°	1764
70°	1539
75°	1440
80°	1263
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7350 cd/sqm

TEST NUMBER: P1286674

CATALOG NUMBER: P3AS05R709030D2WDE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.2	9.8
10°-20°	42.5	24.2
20°-30°	48.4	27.5
30°-40°	37.8	21.5
40°-50°	18.6	10.6
50°-60°	5.7	3.2
60°-70°	3.4	1.9
70°-80°	1.8	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	108.1	61.4
0°-40°	145.9	83.0
0°-60°	170.2	96.8
0°-90°	175.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	175.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	188	
5°	184	17
15°	153	43
25°	106	48
35°	61	38
45°	24	19
55°	6	6
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1286674

CATALOG NUMBER: P3AS05R709030D2WDE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	188.3
2.5°	187.3
5°	184.1
7.5°	179.0
10°	171.6
12.5°	163.0
15°	152.8
17.5°	141.7
20°	130.0
22.5°	117.8
25°	105.8
27.5°	94.0
30°	82.7
32.5°	71.5
35°	60.7
37.5°	50.4
40°	40.6
42.5°	31.6
45°	23.7
47.5°	16.6
50°	10.8
52.5°	7.1
55°	5.9
57.5°	5.1
60°	4.4
62.5°	3.9
65°	3.4
67.5°	2.9
70°	2.4
72.5°	2.0
75°	1.7
77.5°	1.5
80°	1.0
82.5°	0.7
85°	0.5
87.5°	0.2
90°	0.0

(END OF REPORT)