

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286675

Luminaire Tested: P3AS05R709030D2WDE010 E3DLP1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286675
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709030D2WDE010 E3DLP1H
Description: 3in Adjustable Dim to Warm LED luminaire with, R70 optic, 3000K CCT AND, 90CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 359.0 lumens
Efficiency: N/A
Efficacy: 32.3 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286675

CATALOG NUMBER: P3AS05R709030D2WDE010 E3DLP1H

Luminous Intensity Polar Plot



TEST NUMBER: P1286675

CATALOG NUMBER: P3AS05R709030D2WDE010 E3DLP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50			
RCR																				0		
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102	100
1	113	110	107	104		110	107	105	103		103	101	100		100	98	97		96	95	94	92
2	106	101	97	93		104	99	95	92		96	93	90		93	90	88		90	88	86	84
3	100	93	88	83		98	92	87	83		89	85	81		87	83	80		84	81	79	77
4	95	86	80	76		93	85	80	75		83	78	74		81	77	73		79	76	73	71
5	89	80	74	69		88	79	73	69		78	72	68		76	71	68		74	70	67	65
6	85	75	68	64		83	74	68	64		73	67	63		71	66	63		70	65	62	61
7	80	70	64	59		79	69	63	59		68	62	58		67	62	58		66	61	58	56
8	76	66	59	55		75	65	59	55		64	58	54		63	58	54		62	57	54	52
9	72	62	55	51		71	61	55	51		60	55	51		59	54	51		58	54	50	49
10	69	58	52	48		67	58	52	48		57	51	48		56	51	47		55	51	47	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	84204
5°	82654
10°	77954
15°	70738
20°	61885
25°	52188
30°	42741
35°	33140
40°	23730
45°	15009
50°	7505
55°	4588
60°	3947
65°	3632
70°	3206
75°	2965
80°	2526
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15009 cd/sqm

TEST NUMBER: P1286675

CATALOG NUMBER: P3AS05R709030D2WDE010 E3DLP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.0	9.8
10°-20°	86.7	24.1
20°-30°	98.8	27.5
30°-40°	77.2	21.5
40°-50°	37.9	10.6
50°-60°	11.7	3.3
60°-70°	6.9	1.9
70°-80°	3.7	1.0
80°-90°	1.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	220.5	61.4
0°-40°	297.7	82.9
0°-60°	347.3	96.7
0°-90°	359.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	359.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	384	
5°	376	35
15°	312	87
25°	216	99
35°	124	77
45°	48	38
55°	12	12
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1286675

CATALOG NUMBER: P3AS05R709030D2WDE010 E3DLP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	384.0
2.5°	382.0
5°	375.5
7.5°	365.0
10°	350.1
12.5°	332.6
15°	311.6
17.5°	289.1
20°	265.2
22.5°	240.2
25°	215.7
27.5°	191.8
30°	168.8
32.5°	145.8
35°	123.8
37.5°	102.9
40°	82.9
42.5°	64.4
45°	48.4
47.5°	34.0
50°	22.0
52.5°	14.5
55°	12.0
57.5°	10.5
60°	9.0
62.5°	8.0
65°	7.0
67.5°	6.0
70°	5.0
72.5°	4.0
75°	3.5
77.5°	3.0
80°	2.0
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)