

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286711

Luminaire Tested: P3AS09R159030D2WDE010 E3PH1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286711
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R159030D2WDE010 E3PH1MW
Description: 3in Adjustable Dim to Warm LED luminaire with, R15 optic, 3000K CCT AND, 90CRI , E3PH1M'
TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 571.0 lumens
Efficiency: N/A
Efficacy: 38.8 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286711

CATALOG NUMBER: P3AS09R159030D2WDE010 E3PH1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1286711

CATALOG NUMBER: P3AS09R159030D2WDE010 E3PH1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	116	114	113	111	114	112	111	110	108	107	106		105	104	103		101
2	113	110	108	106	111	109	107	105	106	104	103		103	102	100		100
3	111	107	104	102	109	106	103	101	104	101	100		101	100	98		99
4	109	104	101	99	107	103	101	99	102	99	98		100	98	97		98
5	107	102	99	97	105	101	99	96	100	97	96		99	96	95		97
6	105	100	97	95	104	100	97	95	98	96	94		97	95	93		96
7	103	98	95	93	102	98	95	93	97	94	93		96	94	92		95
8	101	97	94	92	101	96	94	92	96	93	91		95	93	91		94
9	100	95	92	90	99	95	92	90	94	92	90		94	91	90		93
10	99	94	91	89	98	94	91	89	93	91	89		93	90	89		92

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1203917
5°	1043823
10°	507517
15°	108264
20°	22752
25°	6775
30°	1469
35°	268
40°	0
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1286711

CATALOG NUMBER: P3AS09R159030D2WDE010 E3PH1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	370.4	64.9
10°-20°	184.2	32.3
20°-30°	15.4	2.7
30°-40°	1.0	0.2
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	570.0	99.8
0°-40°	571.0	100.0
0°-60°	571.0	100.0
0°-90°	571.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	571.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5490	
5°	4742	370
15°	477	184
25°	28	15
35°	1	1
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1286711

CATALOG NUMBER: P3AS09R159030D2WDE010 E3PH1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5490.3
2.5°	5298.2
5°	4742.1
7.5°	3630.9
10°	2279.3
12.5°	1096.7
15°	476.9
17.5°	243.3
20°	97.5
22.5°	48.3
25°	28.0
27.5°	14.5
30°	5.8
32.5°	1.9
35°	1.0
37.5°	1.0
40°	0.0
42.5°	0.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)