

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285966

Luminaire Tested: P3AS13R70B2750DE010 E3DLP1LI_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285966
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R70B2750DE010 E3DLP1LI_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R70 optic, 5000K CCT AND, 80CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 590.0 lumens
Efficiency: N/A
Efficacy: 30.9 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285966
CATALOG NUMBER: P3AS13R70B2750DE010 E3DLP1LI_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1285966
 CATALOG NUMBER: P3AS13R70B2750DE010 E3DLP1LI_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92			92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84			84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77			77
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71			71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65			65
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61			61
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56			56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49			49
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	138388
5°	135857
10°	128098
15°	116255
20°	101696
25°	85771
30°	70239
35°	54475
40°	38987
45°	24685
50°	12315
55°	7531
60°	6491
65°	5967
70°	5257
75°	4829
80°	4167
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 24685 cd/sqm



TEST NUMBER: P1285966
 CATALOG NUMBER: P3AS13R70B2750DE010 E3DLP1LI_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.6	9.8
10°-20°	142.5	24.2
20°-30°	162.3	27.5
30°-40°	126.9	21.5
40°-50°	62.3	10.6
50°-60°	19.2	3.2
60°-70°	11.3	1.9
70°-80°	6.1	1.0
80°-90°	1.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	362.4	61.4
0°-40°	489.3	82.9
0°-60°	570.8	96.7
0°-90°	590.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	590.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	631	
5°	617	58
15°	512	142
25°	354	162
35°	204	127
45°	80	62
55°	20	19
65°	12	11
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1285966
CATALOG NUMBER: P3AS13R70B2750DE010 E3DLP1LI_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	631.1
2.5°	627.8
5°	617.2
7.5°	599.9
10°	575.3
12.5°	546.6
15°	512.1
17.5°	475.2
20°	435.8
22.5°	394.8
25°	354.5
27.5°	315.1
30°	277.4
32.5°	239.6
35°	203.5
37.5°	169.1
40°	136.2
42.5°	105.9
45°	79.6
47.5°	55.8
50°	36.1
52.5°	23.8
55°	19.7
57.5°	17.2
60°	14.8
62.5°	13.1
65°	11.5
67.5°	9.8
70°	8.2
72.5°	6.6
75°	5.7
77.5°	4.9
80°	3.3
82.5°	2.5
85°	1.6
87.5°	0.8
90°	0.0

(END OF REPORT)