

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285997

Luminaire Tested: P3AS02R159030D2WDE010 E3CD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285997
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R159030D2WDE010 E3CD1MW
Description: 3in Adjustable Dim to Warm LED luminaire with, R15 optic, 3000K CCT AND, 90CRI , E3CD1M'
TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 412.0 lumens
Efficiency: N/A
Efficacy: 57.2 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285997

CATALOG NUMBER: P3AS02R159030D2WDE010 E3CD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1285997

CATALOG NUMBER: P3AS02R159030D2WDE010 E3CD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	116	114	112	111	113	112	110	109	108	107	106		104	103	103		101
2	113	110	107	105	111	108	106	104	105	103	101		102	101	99		99
3	110	106	103	100	108	105	102	100	102	100	98		100	98	97		98
4	107	103	100	97	106	102	99	97	100	97	95		98	96	94		97
5	105	100	97	94	104	99	96	94	98	95	93		96	94	92		95
6	103	98	94	92	102	97	94	92	96	93	91		95	92	91		94
7	101	96	92	90	100	95	92	90	94	91	89		93	91	89		92
8	99	94	90	88	98	93	90	88	92	90	88		92	89	87		91
9	97	92	89	87	97	92	89	86	91	88	86		90	88	86		90
10	96	90	87	85	95	90	87	85	89	87	85		89	86	85		88

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	800835
5°	671185
10°	316160
15°	95324
20°	35260
25°	13719
30°	5115
35°	1579
40°	573
45°	310
50°	239
55°	268
60°	307
65°	156
70°	192
75°	254
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 310 cd/sqm

TEST NUMBER: P1285997

CATALOG NUMBER: P3AS02R159030D2WDE010 E3CD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	235.7	57.2
10°-20°	140.1	34.0
20°-30°	29.4	7.1
30°-40°	4.8	1.2
40°-50°	0.8	0.2
50°-60°	0.6	0.2
60°-70°	0.3	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	405.3	98.4
0°-40°	410.1	99.5
0°-60°	411.5	99.9
0°-90°	412.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	412.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3652	
5°	3049	236
15°	420	140
25°	57	29
35°	6	5
45°	1	1
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1285997

CATALOG NUMBER: P3AS02R159030D2WDE010 E3CD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3652.1
1°	3640.7
2°	3582.7
3°	3466.7
4°	3296.7
5°	3049.2
6°	2758.3
7°	2425.7
8°	2108.1
9°	1748.5
10°	1419.9
12.5°	766.1
15°	419.9
17.5°	245.9
20°	151.1
22.5°	92.5
25°	56.7
27.5°	34.2
30°	20.2
32.5°	11.4
35°	5.9
37.5°	3.3
40°	2.0
42.5°	1.3
45°	1.0
47.5°	0.7
50°	0.7
52.5°	0.7
55°	0.7
57.5°	0.7
60°	0.7
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)