

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286718

Luminaire Tested: P3AS09R209030D2WDE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286718
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R209030D2WDE010 E3CD1MMS
Description: 3in Adjustable Dim to Warm LED luminaire with, R20 optic, 3000K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 845.0 lumens
Efficiency: N/A
Efficacy: 57.5 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286718

CATALOG NUMBER: P3AS09R209030D2WDE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1286718

CATALOG NUMBER: P3AS09R209030D2WDE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	116	114	112	110	113	112	110	109	108	106	105		104	103	102		101	100	99	98
2	112	109	106	104	110	108	105	103	104	103	101		102	100	99		99	98	97	95
3	109	105	102	100	108	104	101	99	102	99	97		99	98	96		97	96	95	93
4	107	102	99	96	105	101	98	96	99	97	95		97	95	93		96	94	92	91
5	104	99	96	93	103	98	95	93	97	94	92		95	93	91		94	92	91	90
6	102	97	93	91	101	96	93	90	95	92	90		94	91	89		93	90	89	88
7	100	94	91	88	99	94	91	88	93	90	88		92	89	87		91	89	87	86
8	98	92	89	86	97	92	89	86	91	88	86		90	88	86		89	87	85	85
9	96	90	87	85	95	90	87	85	89	86	84		89	86	84		88	86	84	83
10	94	89	85	83	93	88	85	83	88	85	83		87	84	83		86	84	82	82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1312373
5°	1139112
10°	703839
15°	244474
20°	75070
25°	26542
30°	9824
35°	3935
40°	2118
45°	837
50°	443
55°	497
60°	570
65°	363
70°	449
75°	593
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 837 cd/sqm

TEST NUMBER: P1286718

CATALOG NUMBER: P3AS09R209030D2WDE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	429.5	50.8
10°-20°	340.8	40.3
20°-30°	59.0	7.0
30°-40°	10.7	1.3
40°-50°	2.5	0.3
50°-60°	1.2	0.1
60°-70°	0.8	0.1
70°-80°	0.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	829.3	98.1
0°-40°	840.0	99.4
0°-60°	843.6	99.8
0°-90°	845.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	845.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5985	
5°	5175	429
15°	1077	341
25°	110	59
35°	15	11
45°	3	2
55°	1	1
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1286718

CATALOG NUMBER: P3AS09R209030D2WDE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	5984.9
1°	5956.2
2°	5842.5
3°	5659.9
4°	5445.8
5°	5175.0
6°	4864.6
7°	4503.4
8°	4092.1
9°	3629.9
10°	3161.0
12.5°	1993.9
15°	1076.9
17.5°	575.2
20°	321.7
22.5°	183.9
25°	109.7
27.5°	66.9
30°	38.8
32.5°	22.7
35°	14.7
37.5°	10.0
40°	7.4
42.5°	4.7
45°	2.7
47.5°	1.3
50°	1.3
52.5°	1.3
55°	1.3
57.5°	1.3
60°	1.3
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.7
77.5°	0.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)