

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286753

Luminaire Tested: P3AS09R259030D2WDE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286753
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R259030D2WDE010 E3DL1LI
Description: 3in Adjustable Dim to Warm LED luminaire with, R25 optic, 3000K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 700.0 lumens
Efficiency: N/A
Efficacy: 47.6 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286753

CATALOG NUMBER: P3AS09R259030D2WDE010 E3DL1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1286753

CATALOG NUMBER: P3AS09R259030D2WDE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91
4	101	95	90	87	99	94	89	86	92	88	85		90	87	84		88
5	97	90	85	82	96	89	85	81	88	84	81		86	83	80		85
6	94	86	81	78	92	86	81	78	84	80	77		83	79	77		82
7	90	83	78	74	89	82	77	74	81	77	74		80	76	73		79
8	87	79	74	71	86	79	74	71	78	74	71		77	73	70		76
9	84	76	71	68	83	76	71	68	75	71	68		74	70	68		73
10	81	73	69	65	80	73	68	65	72	68	65		72	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	449021
5°	418929
10°	335598
15°	227811
20°	137842
25°	80593
30°	45906
35°	25243
40°	13397
45°	7039
50°	4094
55°	3058
60°	2631
65°	2802
70°	2565
75°	2288
80°	1642
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7039 cd/sqm

TEST NUMBER: P1286753

CATALOG NUMBER: P3AS09R259030D2WDE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.9	24.1
10°-20°	275.9	39.4
20°-30°	157.6	22.5
30°-40°	62.2	8.9
40°-50°	19.1	2.7
50°-60°	7.5	1.1
60°-70°	5.1	0.7
70°-80°	2.8	0.4
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	602.4	86.1
0°-40°	664.6	94.9
0°-60°	691.2	98.7
0°-90°	700.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	700.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2048	
5°	1903	169
15°	1004	276
25°	333	158
35°	94	62
45°	23	19
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1286753

CATALOG NUMBER: P3AS09R259030D2WDE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	2047.7
1°	2043.7
2°	2027.0
3°	1997.5
4°	1956.7
5°	1903.2
6°	1840.3
7°	1769.4
8°	1687.1
9°	1602.8
10°	1507.2
11°	1412.9
12°	1309.2
13°	1206.8
14°	1101.8
15°	1003.5
17.5°	778.0
20°	590.7
22.5°	443.5
25°	333.1
27.5°	246.8
30°	181.3
32.5°	131.1
35°	94.3
37.5°	66.9
40°	46.8
42.5°	32.1
45°	22.7
47.5°	16.1
50°	12.0
52.5°	9.4
55°	8.0
57.5°	7.4
60°	6.0
62.5°	5.4
65°	5.4
67.5°	4.7
70°	4.0
72.5°	3.3
75°	2.7
77.5°	2.0
80°	1.3
82.5°	1.3
85°	0.7
87.5°	0.7



TEST NUMBER: P1286753

CATALOG NUMBER: P3AS09R259030D2WDE010 E3DL1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)