

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286757

Luminaire Tested: P3AS09R259030D2WDE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286757
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R259030D2WDE010 E3DLD1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 263.0 lumens
Efficiency: N/A
Efficacy: 17.9 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286757

CATALOG NUMBER: P3AS09R259030D2WDE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1286757

CATALOG NUMBER: P3AS09R259030D2WDE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	62495
5°	61017
10°	56534
15°	50352
20°	43264
25°	36776
30°	30283
35°	23584
40°	16975
45°	10761
50°	6379
55°	4396
60°	4035
65°	3736
70°	3334
75°	3050
80°	2904
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 10761 cd/sqm

TEST NUMBER: P1286757

CATALOG NUMBER: P3AS09R259030D2WDE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.7	9.8
10°-20°	61.6	23.4
20°-30°	69.6	26.5
30°-40°	55.0	20.9
40°-50°	27.8	10.6
50°-60°	11.2	4.2
60°-70°	7.1	2.7
70°-80°	3.9	1.5
80°-90°	1.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	156.9	59.6
0°-40°	211.9	80.6
0°-60°	250.8	95.4
0°-90°	263.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	263.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	285	
5°	277	26
15°	222	62
25°	152	70
35°	88	55
45°	35	28
55°	12	11
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1286757

CATALOG NUMBER: P3AS09R259030D2WDE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	285.0
1°	285.0
2°	284.1
3°	282.4
4°	280.1
5°	277.2
6°	273.6
7°	269.3
8°	264.7
9°	259.5
10°	253.9
11°	247.7
12°	241.8
13°	234.9
14°	228.4
15°	221.8
17.5°	203.5
20°	185.4
22.5°	168.4
25°	152.0
27.5°	136.0
30°	119.6
32.5°	104.2
35°	88.1
37.5°	73.4
40°	59.3
42.5°	46.2
45°	34.7
47.5°	25.9
50°	18.7
52.5°	14.1
55°	11.5
57.5°	10.5
60°	9.2
62.5°	8.2
65°	7.2
67.5°	6.2
70°	5.2
72.5°	4.6
75°	3.6
77.5°	2.9
80°	2.3
82.5°	1.6
85°	1.0
87.5°	0.3



TEST NUMBER: P1286757

CATALOG NUMBER: P3AS09R259030D2WDE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)