

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286068

Luminaire Tested: P3AS02R259030D2WDE010 E3DLD1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286068
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259030D2WDE010 E3DLD1H
Description: 3in Adjustable Dim to Warm LED luminaire with, R25 optic, 3000K CCT AND, 90CRI , E3DLD1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 261.0 lumens
Efficiency: N/A
Efficacy: 36.3 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286068
CATALOG NUMBER: P3AS02R259030D2WDE010 E3DLD1H

Luminous Intensity Polar Plot





TEST NUMBER: P1286068
 CATALOG NUMBER: P3AS02R259030D2WDE010 E3DLD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70			70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51			51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48			48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	62035
5°	60555
10°	56111
15°	49966
20°	42937
25°	36510
30°	30055
35°	23423
40°	16860
45°	10699
50°	6311
55°	4358
60°	3991
65°	3736
70°	3334
75°	3050
80°	2904
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10699 cd/sqm



TEST NUMBER: P1286068

CATALOG NUMBER: P3AS02R259030D2WDE010 E3DLD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.5	9.8
10°-20°	61.1	23.4
20°-30°	69.0	26.5
30°-40°	54.6	20.9
40°-50°	27.6	10.6
50°-60°	11.1	4.2
60°-70°	7.1	2.7
70°-80°	3.9	1.5
80°-90°	1.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	155.7	59.6
0°-40°	210.3	80.6
0°-60°	248.9	95.4
0°-90°	261.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	261.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	283	
5°	275	26
15°	220	61
25°	151	69
35°	88	55
45°	34	28
55°	11	11
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1286068
CATALOG NUMBER: P3AS02R259030D2WDE010 E3DLD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	282.9
1°	282.9
2°	281.9
3°	280.3
4°	278.0
5°	275.1
6°	271.5
7°	267.3
8°	262.7
9°	257.5
10°	252.0
11°	245.8
12°	240.0
13°	233.1
14°	226.6
15°	220.1
17.5°	201.9
20°	184.0
22.5°	167.1
25°	150.9
27.5°	134.9
30°	118.7
32.5°	103.4
35°	87.5
37.5°	72.8
40°	58.9
42.5°	45.8
45°	34.5
47.5°	25.7
50°	18.5
52.5°	14.0
55°	11.4
57.5°	10.4
60°	9.1
62.5°	8.1
65°	7.2
67.5°	6.2
70°	5.2
72.5°	4.6
75°	3.6
77.5°	2.9
80°	2.3
82.5°	1.6
85°	1.0
87.5°	0.3



TEST NUMBER: P1286068
CATALOG NUMBER: P3AS02R259030D2WDE010 E3DLD1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)