

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286077

Luminaire Tested: P3AS02R259030D2WDE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286077
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259030D2WDE010 E3DLP1WH
Description: 3in Adjustable Dim to Warm LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 341.0 lumens
Efficiency: N/A
Efficacy: 47.4 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286077
CATALOG NUMBER: P3AS02R259030D2WDE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1286077

CATALOG NUMBER: P3AS02R259030D2WDE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	86	86	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	82	82	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	78	78	78
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75	75	75	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	66	66	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	64	64	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	218732
5°	204072
10°	163479
15°	110965
20°	67159
25°	39268
30°	22358
35°	12287
40°	6527
45°	3442
50°	2013
55°	1491
60°	1272
65°	1349
70°	1282
75°	1101
80°	884
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3442 cd/sqm



TEST NUMBER: P1286077

CATALOG NUMBER: P3AS02R259030D2WDE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.3	24.1
10°-20°	134.4	39.4
20°-30°	76.8	22.5
30°-40°	30.3	8.9
40°-50°	9.3	2.7
50°-60°	3.7	1.1
60°-70°	2.5	0.7
70°-80°	1.4	0.4
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	293.5	86.1
0°-40°	323.8	94.9
0°-60°	336.7	98.7
0°-90°	341.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	341.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	998	
5°	927	82
15°	489	134
25°	162	77
35°	46	30
45°	11	9
55°	4	4
65°	3	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1286077
CATALOG NUMBER: P3AS02R259030D2WDE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	997.5
1°	995.6
2°	987.4
3°	973.1
4°	953.2
5°	927.1
6°	896.5
7°	862.0
8°	821.9
9°	780.8
10°	734.2
11°	688.3
12°	637.8
13°	587.9
14°	536.7
15°	488.8
17.5°	379.0
20°	287.8
22.5°	216.1
25°	162.3
27.5°	120.3
30°	88.3
32.5°	63.9
35°	45.9
37.5°	32.6
40°	22.8
42.5°	15.6
45°	11.1
47.5°	7.8
50°	5.9
52.5°	4.6
55°	3.9
57.5°	3.6
60°	2.9
62.5°	2.6
65°	2.6
67.5°	2.3
70°	2.0
72.5°	1.6
75°	1.3
77.5°	1.0
80°	0.7
82.5°	0.7
85°	0.3
87.5°	0.3



TEST NUMBER: P1286077
CATALOG NUMBER: P3AS02R259030D2WDE010 E3DLP1WH

CANDELA DISTRIBUTION (continued):

90° | $\frac{0^\circ}{0.0}$

(END OF REPORT)