

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286786

Luminaire Tested: P3AS09R309030D2WDE010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286786
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R309030D2WDE010 E3DL1MW
Description: 3in Adjustable Dim to Warm LED luminaire with, R30 optic, 3000K CCT AND, 90CRI , E3DL1M
TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 708.0 lumens
Efficiency: N/A
Efficacy: 48.2 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286786
CATALOG NUMBER: P3AS09R309030D2WDE010 E3DL1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1286786
 CATALOG NUMBER: P3AS09R309030D2WDE010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	86	86	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	82	82	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	78	78	78
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75	75	75	75
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	79	75	73	71	71	71	71
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69	69	69	69
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66	66	66	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	63	63	63	63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	413147
5°	393219
10°	330767
15°	238526
20°	147946
25°	84150
30°	46741
35°	25431
40°	13397
45°	7257
50°	3889
55°	2561
60°	2368
65°	2439
70°	2116
75°	1694
80°	1642
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7257 cd/sqm



TEST NUMBER: P1286786

CATALOG NUMBER: P3AS09R309030D2WDE010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.9	22.7
10°-20°	285.9	40.4
20°-30°	165.3	23.3
30°-40°	62.7	8.9
40°-50°	19.3	2.7
50°-60°	6.5	0.9
60°-70°	4.4	0.6
70°-80°	2.4	0.3
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<hr/>		
0°-30°	612.1	86.4
0°-40°	674.8	95.3
0°-60°	700.5	98.9
0°-90°	708.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	708.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1884	
5°	1786	161
15°	1051	286
25°	348	165
35°	95	63
45°	23	19
55°	7	6
65°	5	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1286786
CATALOG NUMBER: P3AS09R309030D2WDE010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1884.1
1°	1882.7
2°	1871.4
3°	1850.0
4°	1823.2
5°	1786.4
6°	1739.6
7°	1687.4
8°	1629.2
9°	1559.7
10°	1485.5
11°	1405.2
12°	1320.3
13°	1231.3
14°	1141.0
15°	1050.7
17.5°	828.7
20°	634.0
22.5°	470.2
25°	347.8
27.5°	252.8
30°	184.6
32.5°	133.1
35°	95.0
37.5°	66.2
40°	46.8
42.5°	32.8
45°	23.4
47.5°	16.1
50°	11.4
52.5°	8.0
55°	6.7
57.5°	6.0
60°	5.4
62.5°	4.7
65°	4.7
67.5°	4.0
70°	3.3
72.5°	2.7
75°	2.0
77.5°	2.0
80°	1.3
82.5°	1.3
85°	0.7
87.5°	0.0



TEST NUMBER: P1286786
CATALOG NUMBER: P3AS09R309030D2WDE010 E3DL1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)