

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286791

Luminaire Tested: P3AS09R309030D2WDE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286791
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R309030D2WDE010 E3DLD1LI
Description: 3in Adjustable Dim to Warm LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,
E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 545.0 lumens
Efficiency: N/A
Efficacy: 37.1 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286791

CATALOG NUMBER: P3AS09R309030D2WDE010 E3DLD1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1286791

CATALOG NUMBER: P3AS09R309030D2WDE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	85	79	74	92	84	79	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	128762
5°	125864
10°	117054
15°	104155
20°	89584
25°	75900
30°	62997
35°	49416
40°	35409
45°	23227
50°	13236
55°	8678
60°	8201
65°	7627
70°	6860
75°	6270
80°	5935
85°	5032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23227 cd/sqm

TEST NUMBER: P1286791

CATALOG NUMBER: P3AS09R309030D2WDE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.1	9.7
10°-20°	127.5	23.4
20°-30°	143.7	26.4
30°-40°	114.8	21.1
40°-50°	59.0	10.8
50°-60°	22.2	4.1
60°-70°	14.5	2.7
70°-80°	7.9	1.4
80°-90°	2.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	324.4	59.5
0°-40°	439.1	80.6
0°-60°	520.3	95.5
0°-90°	545.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	545.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	587	
5°	572	53
15°	459	128
25°	314	144
35°	185	115
45°	75	59
55°	23	22
65°	15	15
75°	7	8
85°	2	2
90°	0	

TEST NUMBER: P1286791

CATALOG NUMBER: P3AS09R309030D2WDE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	587.2
1°	587.2
2°	585.2
3°	581.8
4°	577.1
5°	571.8
6°	565.1
7°	556.4
8°	547.1
9°	536.4
10°	525.7
11°	513.6
12°	500.9
13°	487.5
14°	473.5
15°	458.8
17.5°	421.3
20°	383.9
22.5°	347.8
25°	313.7
27.5°	280.2
30°	248.8
32.5°	216.7
35°	184.6
37.5°	153.1
40°	123.7
42.5°	97.6
45°	74.9
47.5°	55.5
50°	38.8
52.5°	27.4
55°	22.7
57.5°	20.7
60°	18.7
62.5°	16.7
65°	14.7
67.5°	12.7
70°	10.7
72.5°	8.7
75°	7.4
77.5°	6.0
80°	4.7
82.5°	3.3
85°	2.0
87.5°	0.7



TEST NUMBER: P1286791

CATALOG NUMBER: P3AS09R309030D2WDE010 E3DLD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)