

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286127

Luminaire Tested: P3AS02R359030D2WDE010 E3DLD1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1286127  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R359030D2WDE010 E3DLD1GPH  
Description: 3in Adjustable Dim to Warm LED luminaire with, R35 optic, 3000K CCT AND, 90CRI ,  
E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 129.0 lumens  
Efficiency: N/A  
Efficacy: 17.9 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1286127  
CATALOG NUMBER: P3AS02R359030D2WDE010 E3DLD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1286127

CATALOG NUMBER: P3AS02R359030D2WDE010 E3DLD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91				91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83				83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76				76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69				69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64				64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59				59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55				55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51				51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48				48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45				45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	29471
5°	28835
10°	27009
15°	24245
20°	21095
25°	17977
30°	15066
35°	11993
40°	8673
45°	5489
50°	3002
55°	2064
60°	1974
65°	1816
70°	1731
75°	1525
80°	1389
85°	1258

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 5489 cd/sqm



TEST NUMBER: P1286127

CATALOG NUMBER: P3AS02R359030D2WDE010 E3DLD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	12.2	9.5
10°-20°	29.7	23.0
20°-30°	34.1	26.4
30°-40°	27.8	21.5
40°-50°	14.0	10.9
50°-60°	5.2	4.0
60°-70°	3.5	2.7
70°-80°	1.9	1.5
80°-90°	0.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	76.0	58.9
0°-40°	103.8	80.4
0°-60°	123.0	95.4
0°-90°	129.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	129.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	134	
5°	131	12
15°	107	30
25°	74	34
35°	45	28
45°	18	14
55°	5	5
65°	4	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1286127  
CATALOG NUMBER: P3AS02R359030D2WDE010 E3DLD1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	134.4
1°	134.2
2°	133.9
3°	133.3
4°	132.3
5°	131.0
6°	129.4
7°	127.8
8°	125.8
9°	123.7
10°	121.3
11°	118.8
12°	116.1
13°	113.0
14°	109.8
15°	106.8
17.5°	98.7
20°	90.4
22.5°	81.9
25°	74.3
27.5°	66.8
30°	59.5
32.5°	52.1
35°	44.8
37.5°	37.5
40°	30.3
42.5°	23.6
45°	17.7
47.5°	12.8
50°	8.8
52.5°	6.4
55°	5.4
57.5°	4.9
60°	4.5
62.5°	4.0
65°	3.5
67.5°	3.0
70°	2.7
72.5°	2.2
75°	1.8
77.5°	1.4
80°	1.1
82.5°	0.8
85°	0.5
87.5°	0.3



TEST NUMBER: P1286127

CATALOG NUMBER: P3AS02R359030D2WDE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)