

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286811

Luminaire Tested: P3AS09R359030D2WDE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286811
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R359030D2WDE010 E3DL1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R35 optic, 3000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 345.0 lumens
Efficiency: N/A
Efficacy: 23.5 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286811

CATALOG NUMBER: P3AS09R359030D2WDE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1286811

CATALOG NUMBER: P3AS09R359030D2WDE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	109	107	106	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	91	87	84		89	85	83		87
5	96	89	84	80	95	88	83	80	86	82	79		85	81	78		83
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		80
7	89	81	76	72	88	80	75	72	79	75	71		78	74	71		77
8	85	77	72	69	84	77	72	68	76	71	68		75	71	68		74
9	82	74	69	66	81	74	69	65	73	68	65		72	68	65		71
10	79	71	66	63	78	71	66	63	70	66	63		69	65	62		69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	173999
5°	167224
10°	145711
15°	111601
20°	74673
25°	45172
30°	25928
35°	14482
40°	7700
45°	3969
50°	1910
55°	1491
60°	1447
65°	1193
70°	1282
75°	1101
80°	1263
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3969 cd/sqm

TEST NUMBER: P1286811

CATALOG NUMBER: P3AS09R359030D2WDE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.1	20.0
10°-20°	134.0	38.8
20°-30°	87.7	25.4
30°-40°	35.6	10.3
40°-50°	10.7	3.1
50°-60°	3.6	1.1
60°-70°	2.5	0.7
70°-80°	1.4	0.4
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	290.8	84.3
0°-40°	326.3	94.6
0°-60°	340.6	98.7
0°-90°	345.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	345.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	794	
5°	760	69
15°	492	134
25°	187	88
35°	54	36
45°	13	11
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1286811

CATALOG NUMBER: P3AS09R359030D2WDE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	793.5
1°	792.2
2°	788.6
3°	781.4
4°	772.8
5°	759.7
6°	743.3
7°	724.9
8°	704.3
9°	680.6
10°	654.4
11°	625.2
12°	594.6
13°	560.5
14°	528.0
15°	491.6
17.5°	403.3
20°	320.0
22.5°	246.1
25°	186.7
27.5°	139.1
30°	102.4
32.5°	75.2
35°	54.1
37.5°	38.4
40°	26.9
42.5°	18.7
45°	12.8
47.5°	8.5
50°	5.6
52.5°	4.3
55°	3.9
57.5°	3.6
60°	3.3
62.5°	3.0
65°	2.3
67.5°	2.0
70°	2.0
72.5°	1.6
75°	1.3
77.5°	1.0
80°	1.0
82.5°	0.7
85°	0.3
87.5°	0.3



TEST NUMBER: P1286811

CATALOG NUMBER: P3AS09R359030D2WDE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)