

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286171

Luminaire Tested: P3AS02R459030D2WDE010 E3CB1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286171
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R459030D2WDE010 E3CB1MB
Description: 3in Adjustable Dim to Warm LED luminaire with, R45 optic, 3000K CCT AND, 90CRI , E3CB1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 436.1 lumens
Efficiency: N/A
Efficacy: 60.6 lumens/watt
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286171
CATALOG NUMBER: P3AS02R459030D2WDE010 E3CB1MB

Luminous Intensity Polar Plot





TEST NUMBER: P1286171
 CATALOG NUMBER: P3AS02R459030D2WDE010 E3CB1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91	91	91	91
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	86	86	86	86
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	82	82	82	82
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79	79	79	79
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75	75	75	75
7	90	83	78	74	89	82	78	74	81	77	74	80	76	74	79	76	73	72	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66	66	66	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	64	64	64	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	189020
5°	190028
10°	184209
15°	154348
20°	118007
25°	71835
30°	29878
35°	9583
40°	2977
45°	620
50°	443
55°	497
60°	439
65°	519
70°	449
75°	593
80°	379
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 620 cd/sqm



TEST NUMBER: P1286171

CATALOG NUMBER: P3AS02R459030D2WDE010 E3CB1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.4	18.7
10°-20°	186.9	42.9
20°-30°	134.6	30.9
30°-40°	28.0	6.4
40°-50°	2.6	0.6
50°-60°	1.1	0.2
60°-70°	0.9	0.2
70°-80°	0.6	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	402.9	92.4
0°-40°	430.9	98.8
0°-60°	434.5	99.6
0°-90°	436.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	436.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	862	
5°	863	81
15°	680	187
25°	297	135
35°	36	28
45°	2	3
55°	1	1
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1286171
CATALOG NUMBER: P3AS02R459030D2WDE010 E3CB1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	862.0
2.5°	862.4
5°	863.3
7.5°	857.2
10°	827.3
12.5°	764.8
15°	679.9
17.5°	593.1
20°	505.7
22.5°	405.2
25°	296.9
27.5°	195.8
30°	118.0
32.5°	66.0
35°	35.8
37.5°	20.2
40°	10.4
42.5°	4.6
45°	2.0
47.5°	1.3
50°	1.3
52.5°	1.3
55°	1.3
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.7
77.5°	0.3
80°	0.3
82.5°	0.3
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)