

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286825

Luminaire Tested: P3AS09R359030D2WDE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286825
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R359030D2WDE010 E3DLP1LI
Description: 3in Adjustable Dim to Warm LED luminaire with, R35 optic, 3000K CCT AND, 90CRI ,
E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 434.0 lumens
Efficiency: N/A
Efficacy: 29.5 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286825

CATALOG NUMBER: P3AS09R359030D2WDE010 E3DLP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1286825

CATALOG NUMBER: P3AS09R359030D2WDE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86
4	97	89	83	79	95	88	82	78	86	81	77		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	77	72	68	76	71	67		75	70	67		73
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	70	64	60	78	69	63	59	68	63	59		67	62	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	139506
5°	136055
10°	124402
15°	105585
20°	83587
25°	63221
30°	46032
35°	31133
40°	19122
45°	10978
50°	6618
55°	5352
60°	4693
65°	4151
70°	3398
75°	3389
80°	3410
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10978 cd/sqm

TEST NUMBER: P1286825

CATALOG NUMBER: P3AS09R359030D2WDE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.1	13.2
10°-20°	128.2	29.5
20°-30°	120.0	27.6
30°-40°	73.4	16.9
40°-50°	28.9	6.7
50°-60°	12.7	2.9
60°-70°	7.9	1.8
70°-80°	4.2	1.0
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	305.3	70.3
0°-40°	378.7	87.3
0°-60°	420.4	96.9
0°-90°	434.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	434.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	636	
5°	618	57
15°	465	128
25°	261	120
35°	116	73
45°	35	29
55°	14	13
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1286825

CATALOG NUMBER: P3AS09R359030D2WDE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	636.2
1°	636.8
2°	634.8
3°	630.8
4°	624.8
5°	618.1
6°	609.4
7°	599.4
8°	587.4
9°	574.0
10°	558.7
11°	542.6
12°	525.2
13°	506.5
14°	485.8
15°	465.1
17.5°	411.6
20°	358.2
22.5°	306.7
25°	261.3
27.5°	219.2
30°	181.8
32.5°	147.0
35°	116.3
37.5°	88.9
40°	66.8
42.5°	48.1
45°	35.4
47.5°	25.4
50°	19.4
52.5°	16.0
55°	14.0
57.5°	12.0
60°	10.7
62.5°	9.4
65°	8.0
67.5°	6.7
70°	5.3
72.5°	4.7
75°	4.0
77.5°	3.3
80°	2.7
82.5°	2.0
85°	1.3
87.5°	0.7



TEST NUMBER: P1286825

CATALOG NUMBER: P3AS09R359030D2WDE010 E3DLP1LI

CANDELA DISTRIBUTION (continued):



(END OF REPORT)