

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286843

Luminaire Tested: P3AS09R409030D2WDE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286843
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R409030D2WDE010 E3DL1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R40 optic, 3000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 382.1 lumens
Efficiency: N/A
Efficacy: 26.0 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286843

CATALOG NUMBER: P3AS09R409030D2WDE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1286843

CATALOG NUMBER: P3AS09R409030D2WDE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	99	94	91	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86
5	96	88	83	79	94	88	83	79	86	82	78		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	68	84	76	71	67	75	70	67		74	70	67		73
9	82	73	68	64	81	73	68	64	72	67	64		71	67	64		70
10	78	70	65	62	78	70	65	61	69	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	169022
5°	164120
10°	148940
15°	123043
20°	88744
25°	54898
30°	29726
35°	15366
40°	8359
45°	4683
50°	2354
55°	1759
60°	1579
65°	1557
70°	1475
75°	1356
80°	1263
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4683 cd/sqm

TEST NUMBER: P1286843

CATALOG NUMBER: P3AS09R409030D2WDE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.7	18.0
10°-20°	147.6	38.6
20°-30°	105.3	27.6
30°-40°	38.8	10.2
40°-50°	12.2	3.2
50°-60°	4.3	1.1
60°-70°	2.9	0.8
70°-80°	1.7	0.5
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	321.6	84.2
0°-40°	360.4	94.3
0°-60°	376.9	98.7
0°-90°	382.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	382.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	771	
5°	746	69
15°	542	148
25°	227	105
35°	57	39
45°	15	12
55°	5	4
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1286843

CATALOG NUMBER: P3AS09R409030D2WDE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	770.8
2.5°	764.9
5°	745.6
7.5°	713.5
10°	668.9
12.5°	612.2
15°	542.0
17.5°	463.3
20°	380.3
22.5°	298.7
25°	226.9
27.5°	166.6
30°	117.4
32.5°	82.3
35°	57.4
37.5°	40.7
40°	29.2
42.5°	21.0
45°	15.1
47.5°	10.2
50°	6.9
52.5°	4.9
55°	4.6
57.5°	4.3
60°	3.6
62.5°	3.3
65°	3.0
67.5°	2.6
70°	2.3
72.5°	2.0
75°	1.6
77.5°	1.3
80°	1.0
82.5°	0.7
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)