

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286186

Luminaire Tested: P3AS02R459030D2WDE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286186
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R459030D2WDE010 E3DLD1LI
Description: 3in Adjustable Dim to Warm LED luminaire with, R45 optic, 3000K CCT AND, 90CRI ,
E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 281.9 lumens
Efficiency: N/A
Efficacy: 39.2 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286186
CATALOG NUMBER: P3AS02R459030D2WDE010 E3DLD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1286186
 CATALOG NUMBER: P3AS02R459030D2WDE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91				91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83				83
3	99	92	86	82	97	91	85	81	88	83	80	85	81	78	83	80	77	75				75
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69				69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63				63
6	83	73	66	61	81	72	66	61	71	65	61	69	64	60	68	63	60	58				58
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54				54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	50				50
9	70	60	53	49	69	59	53	49	58	52	48	57	52	48	56	52	48	47				47
10	67	56	50	45	66	56	49	45	55	49	45	54	49	45	53	48	45	44				44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	59798
5°	58728
10°	55577
15°	50693
20°	44827
25°	38930
30°	33398
35°	27840
40°	20753
45°	12683
50°	5868
55°	4588
60°	4429
65°	4047
70°	3719
75°	3558
80°	3283
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12683 cd/sqm



TEST NUMBER: P1286186
 CATALOG NUMBER: P3AS02R459030D2WDE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.9	8.8
10°-20°	62.2	22.1
20°-30°	73.8	26.2
30°-40°	64.2	22.8
40°-50°	32.2	11.4
50°-60°	11.2	4.0
60°-70°	7.8	2.8
70°-80°	4.4	1.5
80°-90°	1.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	160.9	57.1
0°-40°	225.1	79.9
0°-60°	268.4	95.2
0°-90°	281.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	281.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	273	
5°	267	25
15°	223	62
25°	161	74
35°	104	64
45°	41	32
55°	12	11
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1286186
CATALOG NUMBER: P3AS02R459030D2WDE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	272.7
2.5°	271.4
5°	266.8
7.5°	259.7
10°	249.6
12.5°	237.2
15°	223.3
17.5°	207.7
20°	192.1
22.5°	176.1
25°	160.9
27.5°	146.2
30°	131.9
32.5°	118.3
35°	104.0
37.5°	88.7
40°	72.5
42.5°	56.5
45°	40.9
47.5°	27.0
50°	17.2
52.5°	13.3
55°	12.0
57.5°	11.0
60°	10.1
62.5°	9.1
65°	7.8
67.5°	6.8
70°	5.8
72.5°	4.9
75°	4.2
77.5°	3.2
80°	2.6
82.5°	1.9
85°	1.0
87.5°	0.6
90°	0.0

(END OF REPORT)