

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286193

Luminaire Tested: P3AS02R459030D2WDE010 E3DLP1MW

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1286193  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R459030D2WDE010 E3DLP1MW  
Description: 3in Adjustable Dim to Warm LED luminaire with, R45 optic, 3000K CCT AND, 90CRI ,  
E3DLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 235.0 lumens  
Efficiency: N/A  
Efficacy: 32.6 lumens/watt  
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1286193

CATALOG NUMBER: P3AS02R459030D2WDE010 E3DLP1MW

### Luminous Intensity Polar Plot



TEST NUMBER: P1286193

CATALOG NUMBER: P3AS02R459030D2WDE010 E3DLP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 103 | 104 | 102 | 100 |  | 100 | 99  | 97  |  | 97  |
| 2   | 107 | 102 | 98  | 94  | 105 | 100 | 96  | 93  | 97  | 94  | 91  |  | 94  | 91  | 89  |  | 91  |
| 3   | 102 | 95  | 90  | 85  | 100 | 93  | 89  | 85  | 91  | 87  | 83  |  | 88  | 85  | 82  |  | 86  |
| 4   | 96  | 88  | 83  | 78  | 94  | 87  | 82  | 78  | 85  | 81  | 77  |  | 83  | 79  | 76  |  | 81  |
| 5   | 91  | 83  | 77  | 72  | 90  | 82  | 76  | 72  | 80  | 75  | 71  |  | 78  | 74  | 71  |  | 77  |
| 6   | 87  | 78  | 72  | 67  | 85  | 77  | 71  | 67  | 75  | 70  | 66  |  | 74  | 69  | 66  |  | 73  |
| 7   | 83  | 73  | 67  | 63  | 81  | 72  | 67  | 62  | 71  | 66  | 62  |  | 70  | 65  | 62  |  | 69  |
| 8   | 79  | 69  | 63  | 59  | 77  | 68  | 63  | 59  | 67  | 62  | 58  |  | 66  | 62  | 58  |  | 65  |
| 9   | 75  | 65  | 59  | 55  | 74  | 65  | 59  | 55  | 64  | 59  | 55  |  | 63  | 58  | 55  |  | 62  |
| 10  | 72  | 62  | 56  | 52  | 71  | 61  | 56  | 52  | 61  | 55  | 52  |  | 60  | 55  | 52  |  | 59  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 69994 |
| 5°  | 68391 |
| 10° | 63103 |
| 15° | 54870 |
| 20° | 45084 |
| 25° | 35058 |
| 30° | 25903 |
| 35° | 18230 |
| 40° | 11364 |
| 45° | 6171  |
| 50° | 3343  |
| 55° | 2867  |
| 60° | 2588  |
| 65° | 2179  |
| 70° | 1859  |
| 75° | 1949  |
| 80° | 1642  |
| 85° | 1761  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6171 cd/sqm

TEST NUMBER: P1286193

CATALOG NUMBER: P3AS02R459030D2WDE010 E3DLP1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 28.8   | 12.2      |
| 10°-20°   | 66.8   | 28.4      |
| 20°-30°   | 66.3   | 28.2      |
| 30°-40°   | 42.7   | 18.2      |
| 40°-50°   | 16.5   | 7.0       |
| 50°-60°   | 6.7    | 2.8       |
| 60°-70°   | 4.2    | 1.8       |
| 70°-80°   | 2.3    | 1.0       |
| 80°-90°   | 0.7    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 161.9  | 68.9      |
| 0°-40°    | 204.6  | 87.1      |
| 0°-60°    | 227.8  | 96.9      |
| 0°-90°    | 235.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 235.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 319 |      |
| 5°  | 311 | 29   |
| 15° | 242 | 67   |
| 25° | 145 | 66   |
| 35° | 68  | 43   |
| 45° | 20  | 16   |
| 55° | 8   | 7    |
| 65° | 4   | 4    |
| 75° | 2   | 2    |
| 85° | 1   | 1    |
| 90° | 0   |      |

TEST NUMBER: P1286193

CATALOG NUMBER: P3AS02R459030D2WDE010 E3DLP1MW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 319.2 |
| 2.5°  | 317.6 |
| 5°    | 310.7 |
| 7.5°  | 299.0 |
| 10°   | 283.4 |
| 12.5° | 263.8 |
| 15°   | 241.7 |
| 17.5° | 217.6 |
| 20°   | 193.2 |
| 22.5° | 168.4 |
| 25°   | 144.9 |
| 27.5° | 122.8 |
| 30°   | 102.3 |
| 32.5° | 84.4  |
| 35°   | 68.1  |
| 37.5° | 53.4  |
| 40°   | 39.7  |
| 42.5° | 28.7  |
| 45°   | 19.9  |
| 47.5° | 13.4  |
| 50°   | 9.8   |
| 52.5° | 8.1   |
| 55°   | 7.5   |
| 57.5° | 6.5   |
| 60°   | 5.9   |
| 62.5° | 4.9   |
| 65°   | 4.2   |
| 67.5° | 3.6   |
| 70°   | 2.9   |
| 72.5° | 2.6   |
| 75°   | 2.3   |
| 77.5° | 1.6   |
| 80°   | 1.3   |
| 82.5° | 1.0   |
| 85°   | 0.7   |
| 87.5° | 0.3   |
| 90°   | 0.0   |

(END OF REPORT)