

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286211

Luminaire Tested: P3AS02R509030D2WDE010 E3DL1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286211
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R509030D2WDE010 E3DL1WH
Description: 3in Adjustable Dim to Warm LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3DL1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 240.0 lumens
Efficiency: N/A
Efficacy: 33.3 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286211
CATALOG NUMBER: P3AS02R509030D2WDE010 E3DL1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1286211
 CATALOG NUMBER: P3AS02R509030D2WDE010 E3DL1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79				79
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73				73
5	91	83	76	72	90	82	76	72	80	75	71	78	74	70	77	73	70	68				68
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64				64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60				60
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56				56
9	75	65	59	55	74	64	59	55	63	58	55	63	58	54	62	57	54	53				53
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50				50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	69797
5°	67929
10°	62635
15°	55074
20°	46087
25°	36534
30°	26814
35°	18444
40°	11708
45°	6543
50°	3548
55°	2982
60°	2544
65°	2335
70°	2052
75°	1949
80°	1642
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6543 cd/sqm



TEST NUMBER: P1286211

CATALOG NUMBER: P3AS02R509030D2WDE010 E3DL1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.6	11.9
10°-20°	67.2	28.0
20°-30°	68.7	28.6
30°-40°	43.6	18.2
40°-50°	17.3	7.2
50°-60°	7.0	2.9
60°-70°	4.5	1.9
70°-80°	2.3	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	164.5	68.6
0°-40°	208.1	86.7
0°-60°	232.5	96.9
0°-90°	240.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	240.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	318	
5°	309	29
15°	243	67
25°	151	69
35°	69	44
45°	21	17
55°	8	7
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1286211
CATALOG NUMBER: P3AS02R509030D2WDE010 E3DL1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	318.3
2.5°	316.1
5°	308.6
7.5°	296.9
10°	281.3
12.5°	262.8
15°	242.6
17.5°	220.6
20°	197.5
22.5°	174.4
25°	151.0
27.5°	127.7
30°	105.9
32.5°	86.4
35°	68.9
37.5°	53.9
40°	40.9
42.5°	30.2
45°	21.1
47.5°	14.3
50°	10.4
52.5°	8.8
55°	7.8
57.5°	6.8
60°	5.8
62.5°	5.2
65°	4.5
67.5°	3.9
70°	3.2
72.5°	2.6
75°	2.3
77.5°	1.6
80°	1.3
82.5°	1.0
85°	0.6
87.5°	0.3
90°	0.0

(END OF REPORT)