

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286914

Luminaire Tested: P3AS09R509030D2WDE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286914
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R509030D2WDE010 E3DLP1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R50 optic, 3000K CCT AND, 90CRI ,
E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 494.0 lumens
Efficiency: N/A
Efficacy: 33.6 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286914
CATALOG NUMBER: P3AS09R509030D2WDE010 E3DLP1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1286914
 CATALOG NUMBER: P3AS09R509030D2WDE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79				79
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73				73
5	91	83	76	72	90	82	76	72	80	75	71	78	74	70	77	73	70	68				68
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64				64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60				60
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56				56
9	75	65	59	55	74	64	59	55	63	58	55	63	58	54	62	57	54	53				53
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50				50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	143673
5°	139819
10°	128922
15°	113372
20°	94858
25°	75222
30°	55198
35°	37932
40°	24102
45°	13490
50°	7300
55°	6117
60°	5263
65°	4877
70°	4296
75°	3982
80°	3410
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13490 cd/sqm



TEST NUMBER: P1286914

CATALOG NUMBER: P3AS09R509030D2WDE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.8	11.9
10°-20°	138.3	28.0
20°-30°	141.5	28.6
30°-40°	89.7	18.2
40°-50°	35.7	7.2
50°-60°	14.5	2.9
60°-70°	9.3	1.9
70°-80°	4.7	1.0
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	338.6	68.6
0°-40°	428.4	86.7
0°-60°	478.5	96.9
0°-90°	494.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	494.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	655	
5°	635	59
15°	499	138
25°	311	141
35°	142	90
45°	44	36
55°	16	14
65°	9	9
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1286914

CATALOG NUMBER: P3AS09R509030D2WDE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	655.2
2.5°	650.5
5°	635.2
7.5°	611.1
10°	579.0
12.5°	540.9
15°	499.4
17.5°	454.0
20°	406.5
22.5°	359.0
25°	310.9
27.5°	262.8
30°	218.0
32.5°	177.8
35°	141.7
37.5°	111.0
40°	84.2
42.5°	62.2
45°	43.5
47.5°	29.4
50°	21.4
52.5°	18.1
55°	16.0
57.5°	14.0
60°	12.0
62.5°	10.7
65°	9.4
67.5°	8.0
70°	6.7
72.5°	5.3
75°	4.7
77.5°	3.3
80°	2.7
82.5°	2.0
85°	1.3
87.5°	0.7
90°	0.0

(END OF REPORT)