

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286241

Luminaire Tested: P3AS02R559030D2WDE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286241
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R559030D2WDE010 E3DL1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R55 optic, 3000K CCT AND, 90CRI ,
E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 355.0 lumens
Efficiency: N/A
Efficacy: 49.3 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286241

CATALOG NUMBER: P3AS02R559030D2WDE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1286241

CATALOG NUMBER: P3AS02R559030D2WDE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87		
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	85	82	81		
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	82	79	77	75		
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70		
6	88	79	73	69	86	78	73	68	77	72	68	75	71	68	74	70	67	66		
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62		
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58		
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55		
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	97470
5°	96500
10°	93185
15°	86130
20°	74323
25°	58697
30°	41652
35°	26850
40°	16116
45°	9086
50°	4878
55°	1759
60°	1579
65°	1505
70°	1475
75°	1356
80°	1263
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9086 cd/sqm

TEST NUMBER: P1286241

CATALOG NUMBER: P3AS02R559030D2WDE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.2	11.6
10°-20°	104.9	29.6
20°-30°	110.0	31.0
30°-40°	64.1	18.1
40°-50°	24.0	6.8
50°-60°	5.6	1.6
60°-70°	2.9	0.8
70°-80°	1.7	0.5
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	256.1	72.1
0°-40°	320.2	90.2
0°-60°	349.9	98.6
0°-90°	355.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	355.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	444	
5°	438	41
15°	379	105
25°	243	110
35°	100	64
45°	29	24
55°	5	6
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1286241

CATALOG NUMBER: P3AS02R559030D2WDE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	444.5
2.5°	443.2
5°	438.4
7.5°	430.5
10°	418.5
12.5°	401.6
15°	379.4
17.5°	351.4
20°	318.5
22.5°	281.7
25°	242.6
27.5°	202.6
30°	164.5
32.5°	129.9
35°	100.3
37.5°	76.2
40°	56.3
42.5°	40.4
45°	29.3
47.5°	21.2
50°	14.3
52.5°	8.1
55°	4.6
57.5°	3.9
60°	3.6
62.5°	3.3
65°	2.9
67.5°	2.6
70°	2.3
72.5°	2.0
75°	1.6
77.5°	1.3
80°	1.0
82.5°	0.7
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)