

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286926

Luminaire Tested: P3AS09R559030D2WDE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286926
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R559030D2WDE010 E3DL1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R55 optic, 3000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 357.0 lumens
Efficiency: N/A
Efficacy: 24.3 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286926

CATALOG NUMBER: P3AS09R559030D2WDE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1286926

CATALOG NUMBER: P3AS09R559030D2WDE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	86	78	73	68	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	98040
5°	97028
10°	93697
15°	86607
20°	74743
25°	59036
30°	41880
35°	27010
40°	16230
45°	9148
50°	4912
55°	1759
60°	1579
65°	1505
70°	1475
75°	1356
80°	1263
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9148 cd/sqm

TEST NUMBER: P1286926

CATALOG NUMBER: P3AS09R559030D2WDE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.5	11.6
10°-20°	105.5	29.6
20°-30°	110.6	31.0
30°-40°	64.5	18.1
40°-50°	24.1	6.8
50°-60°	5.7	1.6
60°-70°	2.9	0.8
70°-80°	1.7	0.5
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	257.5	72.1
0°-40°	322.0	90.2
0°-60°	351.9	98.6
0°-90°	357.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	357.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	447	
5°	441	41
15°	382	106
25°	244	111
35°	101	65
45°	30	24
55°	5	6
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1286926

CATALOG NUMBER: P3AS09R559030D2WDE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	447.1
2.5°	445.7
5°	440.8
7.5°	433.0
10°	420.8
12.5°	403.8
15°	381.5
17.5°	353.4
20°	320.3
22.5°	283.3
25°	244.0
27.5°	203.7
30°	165.4
32.5°	130.7
35°	100.9
37.5°	76.6
40°	56.7
42.5°	40.6
45°	29.5
47.5°	21.3
50°	14.4
52.5°	8.2
55°	4.6
57.5°	3.9
60°	3.6
62.5°	3.3
65°	2.9
67.5°	2.6
70°	2.3
72.5°	2.0
75°	1.6
77.5°	1.3
80°	1.0
82.5°	0.7
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)