

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286292

Luminaire Tested: P3AS02R659030D2WDE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286292
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R659030D2WDE010 E3D1WH
Description: 3in Adjustable Dim to Warm LED luminaire with, R65 optic, 3000K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 388.0 lumens
Efficiency: N/A
Efficacy: 53.9 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286292
CATALOG NUMBER: P3AS02R659030D2WDE010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1286292
 CATALOG NUMBER: P3AS02R659030D2WDE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94			94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82			82
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	77			77
5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72			72
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			67
7	84	75	70	65	83	75	69	65	73	69	65	72	68	65	71	67	64	63			63
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59			59
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56			56
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	103961
5°	96544
10°	93363
15°	89966
20°	83167
25°	75779
30°	58541
35°	33943
40°	13454
45°	5737
50°	1365
55°	191
60°	132
65°	104
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5737 cd/sqm



TEST NUMBER: P1286292

CATALOG NUMBER: P3AS02R659030D2WDE010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.4	10.7
10°-20°	110.4	28.5
20°-30°	139.7	36.0
30°-40°	79.6	20.5
40°-50°	15.8	4.1
50°-60°	0.8	0.2
60°-70°	0.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	291.5	75.1
0°-40°	371.1	95.7
0°-60°	387.7	99.9
0°-90°	388.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	388.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	474	
5°	439	41
15°	396	110
25°	313	140
35°	127	80
45°	18	16
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1286292

CATALOG NUMBER: P3AS02R659030D2WDE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	474.1
1°	470.6
2°	463.0
3°	454.0
4°	445.3
5°	438.6
6°	433.6
7°	429.6
8°	426.1
9°	422.6
10°	419.3
11°	415.6
12°	411.8
13°	407.1
14°	402.2
15°	396.3
16°	389.3
17°	381.6
18°	373.3
19°	364.6
20°	356.4
21°	348.1
22°	340.6
23°	332.8
24°	323.7
25°	313.2
26°	300.6
27°	285.5
28°	268.4
29°	250.2
30°	231.2
31°	210.4
32°	189.6
32.5°	178.9
33°	168.6
34°	147.5
35°	126.8
36°	107.6
37°	88.7
37.5°	78.9
38°	71.1
39°	57.6
40°	47.0
42.5°	29.0
45°	18.5



TEST NUMBER: P1286292
CATALOG NUMBER: P3AS02R659030D2WDE010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	10.8
50°	4.0
52.5°	0.8
55°	0.5
57.5°	0.3
60°	0.3
62.5°	0.3
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)