

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286294

Luminaire Tested: P3AS02R659030D2WDE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286294
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R659030D2WDE010 E3DL1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 160.0 lumens
Efficiency: N/A
Efficacy: 22.2 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286294

CATALOG NUMBER: P3AS02R659030D2WDE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1286294

CATALOG NUMBER: P3AS02R659030D2WDE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	59	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	37738
5°	37288
10°	35871
15°	33598
20°	30219
25°	25671
30°	20079
35°	14295
40°	9360
45°	5799
50°	2934
55°	1032
60°	921
65°	934
70°	833
75°	847
80°	758
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5799 cd/sqm

TEST NUMBER: P1286294

CATALOG NUMBER: P3AS02R659030D2WDE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.9	9.9
10°-20°	41.2	25.7
20°-30°	48.1	30.1
30°-40°	33.6	21.0
40°-50°	14.8	9.3
50°-60°	3.3	2.1
60°-70°	1.7	1.1
70°-80°	1.0	0.6
80°-90°	0.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	105.2	65.8
0°-40°	138.9	86.8
0°-60°	157.0	98.1
0°-90°	160.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	160.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	172	
5°	169	16
15°	148	41
25°	106	48
35°	53	34
45°	19	15
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1286294

CATALOG NUMBER: P3AS02R659030D2WDE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	172.1
2.5°	171.4
5°	169.4
7.5°	165.9
10°	161.1
12.5°	155.2
15°	148.0
17.5°	139.2
20°	129.5
22.5°	118.5
25°	106.1
27.5°	93.0
30°	79.3
32.5°	66.0
35°	53.4
37.5°	42.4
40°	32.7
42.5°	24.7
45°	18.7
47.5°	13.7
50°	8.6
52.5°	4.5
55°	2.7
57.5°	2.4
60°	2.1
62.5°	1.9
65°	1.8
67.5°	1.4
70°	1.3
72.5°	1.1
75°	1.0
77.5°	0.8
80°	0.6
82.5°	0.5
85°	0.3
87.5°	0.2
90°	0.0

(END OF REPORT)