

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286996

Luminaire Tested: P3AS09R659030D2WDE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286996
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R659030D2WDE010 E3DLP1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 227.0 lumens
Efficiency: N/A
Efficacy: 15.4 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286996

CATALOG NUMBER: P3AS09R659030D2WDE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1286996

CATALOG NUMBER: P3AS09R659030D2WDE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		90
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	57693
5°	56262
10°	52393
15°	46947
20°	40557
25°	33728
30°	26612
35°	19702
40°	13597
45°	8435
50°	4571
55°	2867
60°	2456
65°	2231
70°	1859
75°	1694
80°	1642
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8435 cd/sqm

TEST NUMBER: P1286996

CATALOG NUMBER: P3AS09R659030D2WDE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.8	10.5
10°-20°	57.5	25.3
20°-30°	63.6	28.0
30°-40°	46.2	20.3
40°-50°	21.6	9.5
50°-60°	7.3	3.2
60°-70°	4.2	1.9
70°-80°	2.2	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	144.8	63.8
0°-40°	191.0	84.1
0°-60°	219.9	96.9
0°-90°	227.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	227.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	263	
5°	256	24
15°	207	57
25°	139	64
35°	74	46
45°	27	22
55°	8	7
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1286996

CATALOG NUMBER: P3AS09R659030D2WDE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	263.1
2.5°	261.5
5°	255.6
7.5°	246.8
10°	235.3
12.5°	221.9
15°	206.8
17.5°	190.5
20°	173.8
22.5°	156.4
25°	139.4
27.5°	122.1
30°	105.1
32.5°	88.7
35°	73.6
37.5°	59.9
40°	47.5
42.5°	36.3
45°	27.2
47.5°	19.6
50°	13.4
52.5°	9.2
55°	7.5
57.5°	6.5
60°	5.6
62.5°	4.9
65°	4.3
67.5°	3.6
70°	2.9
72.5°	2.6
75°	2.0
77.5°	1.6
80°	1.3
82.5°	1.0
85°	0.7
87.5°	0.3
90°	0.0

(END OF REPORT)