

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286323

Luminaire Tested: P3AS02R709030D2WDE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286323
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R709030D2WDE010 E3DL1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R70 optic, 3000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 161.0 lumens
Efficiency: N/A
Efficacy: 22.4 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286323
CATALOG NUMBER: P3AS02R709030D2WDE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1286323
 CATALOG NUMBER: P3AS02R709030D2WDE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77	77	77	77
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70	70	70	70
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65	65	65	65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60	60	60	60
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55
8	75	65	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51	51	51	51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48	48	48	48
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44	44	44	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	31160
5°	30795
10°	29904
15°	28627
20°	26836
25°	24364
30°	21041
35°	16784
40°	12223
45°	8032
50°	3753
55°	1147
60°	1140
65°	1090
70°	1026
75°	1101
80°	1010
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8032 cd/sqm



TEST NUMBER: P1286323

CATALOG NUMBER: P3AS02R709030D2WDE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	13.2	8.2
10°-20°	35.3	21.9
20°-30°	45.9	28.5
30°-40°	38.9	24.2
40°-50°	20.1	12.5
50°-60°	3.9	2.4
60°-70°	2.1	1.3
70°-80°	1.3	0.8
80°-90°	0.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	94.4	58.6
0°-40°	133.3	82.8
0°-60°	157.2	97.7
0°-90°	161.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	161.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	142	
5°	140	13
15°	126	35
25°	101	46
35°	63	39
45°	26	20
55°	3	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1286323
CATALOG NUMBER: P3AS02R709030D2WDE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	142.1
2.5°	141.7
5°	139.9
7.5°	137.3
10°	134.3
12.5°	130.5
15°	126.1
17.5°	120.9
20°	115.0
22.5°	108.2
25°	100.7
27.5°	92.3
30°	83.1
32.5°	73.1
35°	62.7
37.5°	52.4
40°	42.7
42.5°	33.6
45°	25.9
47.5°	19.0
50°	11.0
52.5°	4.8
55°	3.0
57.5°	2.9
60°	2.6
62.5°	2.4
65°	2.1
67.5°	1.9
70°	1.6
72.5°	1.4
75°	1.3
77.5°	1.0
80°	0.8
82.5°	0.5
85°	0.3
87.5°	0.2
90°	0.0

(END OF REPORT)