

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287018

Luminaire Tested: P3AS09R709030D2WDE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287018
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R709030D2WDE010 E3DL1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R70 optic, 3000K CCT AND, 90CRI ,
E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 674.0 lumens
Efficiency: N/A
Efficacy: 45.8 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287018

CATALOG NUMBER: P3AS09R709030D2WDE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1287018

CATALOG NUMBER: P3AS09R709030D2WDE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	53	74	64	58	53	63	57	53		62	57	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	49	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	130472
5°	128923
10°	125181
15°	119887
20°	112313
25°	102030
30°	88140
35°	70242
40°	51153
45°	33616
50°	15761
55°	4855
60°	4693
65°	4514
70°	4296
75°	4575
80°	4167
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 33616 cd/sqm

TEST NUMBER: P1287018

CATALOG NUMBER: P3AS09R709030D2WDE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.2	8.2
10°-20°	147.8	21.9
20°-30°	192.1	28.5
30°-40°	163.0	24.2
40°-50°	84.1	12.5
50°-60°	16.2	2.4
60°-70°	8.8	1.3
70°-80°	5.4	0.8
80°-90°	1.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	395.1	58.6
0°-40°	558.1	82.8
0°-60°	658.3	97.7
0°-90°	674.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	674.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	595	
5°	586	55
15°	528	148
25°	422	192
35°	262	163
45°	108	84
55°	13	16
65°	9	9
75°	5	5
85°	1	2
90°	0	

TEST NUMBER: P1287018

CATALOG NUMBER: P3AS09R709030D2WDE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	595.0
2.5°	593.0
5°	585.7
7.5°	575.0
10°	562.2
12.5°	546.2
15°	528.1
17.5°	506.0
20°	481.3
22.5°	453.1
25°	421.7
27.5°	386.2
30°	348.1
32.5°	305.9
35°	262.4
37.5°	219.5
40°	178.7
42.5°	140.6
45°	108.4
47.5°	79.7
50°	46.2
52.5°	20.1
55°	12.7
57.5°	12.0
60°	10.7
62.5°	10.0
65°	8.7
67.5°	8.0
70°	6.7
72.5°	6.0
75°	5.4
77.5°	4.0
80°	3.3
82.5°	2.0
85°	1.3
87.5°	0.7
90°	0.0

(END OF REPORT)