

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287044

Luminaire Tested: P3AS13R159030D2WDE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287044
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R159030D2WDE010 E3DLD1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 416.0 lumens
Efficiency: N/A
Efficacy: 20.7 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287044

CATALOG NUMBER: P3AS13R159030D2WDE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1287044

CATALOG NUMBER: P3AS13R159030D2WDE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	67		75	71	67		74
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69
7	80	69	63	58	78	69	63	58	67	62	58		66	61	57		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	104926
5°	102091
10°	93296
15°	81703
20°	70099
25°	58528
30°	46843
35°	35121
40°	25505
45°	16684
50°	10439
55°	7034
60°	6228
65°	5759
70°	5386
75°	4914
80°	4672
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16684 cd/sqm

TEST NUMBER: P1287044

CATALOG NUMBER: P3AS13R159030D2WDE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.8	10.3
10°-20°	100.3	24.1
20°-30°	110.5	26.6
30°-40°	82.7	19.9
40°-50°	42.9	10.3
50°-60°	17.8	4.3
60°-70°	11.0	2.6
70°-80°	6.2	1.5
80°-90°	1.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	253.6	61.0
0°-40°	336.3	80.9
0°-60°	397.0	95.4
0°-90°	416.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	416.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	478	
5°	464	43
15°	360	100
25°	242	111
35°	131	83
45°	54	43
55°	18	18
65°	11	11
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1287044

CATALOG NUMBER: P3AS13R159030D2WDE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	478.5
1°	479.0
2°	477.5
3°	474.3
4°	469.6
5°	463.8
6°	456.4
7°	448.5
8°	439.0
9°	429.0
10°	419.0
12.5°	390.0
15°	359.9
17.5°	329.9
20°	300.4
22.5°	270.4
25°	241.9
27.5°	213.4
30°	185.0
32.5°	157.0
35°	131.2
37.5°	109.1
40°	89.1
42.5°	70.6
45°	53.8
47.5°	40.6
50°	30.6
52.5°	22.7
55°	18.4
57.5°	16.3
60°	14.2
62.5°	12.6
65°	11.1
67.5°	9.5
70°	8.4
72.5°	6.9
75°	5.8
77.5°	4.7
80°	3.7
82.5°	2.6
85°	1.6
87.5°	0.5
90°	0.0

(END OF REPORT)