

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286354

Luminaire Tested: P3AS05R159030D2WDE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286354
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R159030D2WDE010 E3DLD1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 193.0 lumens
Efficiency: N/A
Efficacy: 17.4 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286354

CATALOG NUMBER: P3AS05R159030D2WDE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1286354

CATALOG NUMBER: P3AS05R159030D2WDE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	67		75	71	67		74
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69
7	80	70	63	58	78	69	63	58	67	62	58		66	61	58		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	48680
5°	47369
10°	43286
15°	37912
20°	32529
25°	27147
30°	21725
35°	16302
40°	11822
45°	7722
50°	4844
55°	3288
60°	2895
65°	2646
70°	2500
75°	2288
80°	2147
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7722 cd/sqm

TEST NUMBER: P1286354

CATALOG NUMBER: P3AS05R159030D2WDE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.9	10.3
10°-20°	46.5	24.1
20°-30°	51.3	26.6
30°-40°	38.4	19.9
40°-50°	19.9	10.3
50°-60°	8.3	4.3
60°-70°	5.1	2.6
70°-80°	2.9	1.5
80°-90°	0.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	117.6	61.0
0°-40°	156.0	80.9
0°-60°	184.2	95.4
0°-90°	193.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	193.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	222	
5°	215	20
15°	167	47
25°	112	51
35°	61	38
45°	25	20
55°	9	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1286354

CATALOG NUMBER: P3AS05R159030D2WDE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	222.0
1°	222.3
2°	221.5
3°	220.1
4°	217.8
5°	215.2
6°	211.7
7°	208.1
8°	203.7
9°	199.0
10°	194.4
12.5°	180.9
15°	167.0
17.5°	153.1
20°	139.4
22.5°	125.4
25°	112.2
27.5°	99.0
30°	85.8
32.5°	72.9
35°	60.9
37.5°	50.6
40°	41.3
42.5°	32.8
45°	24.9
47.5°	18.8
50°	14.2
52.5°	10.5
55°	8.6
57.5°	7.6
60°	6.6
62.5°	5.9
65°	5.1
67.5°	4.4
70°	3.9
72.5°	3.2
75°	2.7
77.5°	2.2
80°	1.7
82.5°	1.2
85°	0.7
87.5°	0.2
90°	0.0

(END OF REPORT)