

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286359

Luminaire Tested: P3AS05R159030D2WDE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286359
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R159030D2WDE010 E3DLD1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,
E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 394.0 lumens
Efficiency: N/A
Efficacy: 35.5 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286359

CATALOG NUMBER: P3AS05R159030D2WDE010 E3DLD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1286359

CATALOG NUMBER: P3AS05R159030D2WDE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	67		75	70	67		74
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69
7	80	69	63	58	78	69	63	58	67	62	58		66	61	57		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99378
5°	96676
10°	88353
15°	77390
20°	66389
25°	55431
30°	44361
35°	33274
40°	24160
45°	15785
50°	9859
55°	6690
60°	5921
65°	5448
70°	5129
75°	4660
80°	4420
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15785 cd/sqm

TEST NUMBER: P1286359

CATALOG NUMBER: P3AS05R159030D2WDE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.5	10.3
10°-20°	95.0	24.1
20°-30°	104.7	26.6
30°-40°	78.4	19.9
40°-50°	40.6	10.3
50°-60°	16.9	4.3
60°-70°	10.4	2.7
70°-80°	5.9	1.5
80°-90°	1.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	240.2	61.0
0°-40°	318.6	80.8
0°-60°	376.0	95.4
0°-90°	394.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	394.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	453	
5°	439	41
15°	341	95
25°	229	105
35°	124	78
45°	51	41
55°	18	17
65°	10	10
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1286359

CATALOG NUMBER: P3AS05R159030D2WDE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	453.2
1°	453.7
2°	452.2
3°	449.2
4°	444.7
5°	439.2
6°	432.3
7°	424.8
8°	415.8
9°	406.3
10°	396.8
12.5°	369.4
15°	340.9
17.5°	312.5
20°	284.5
22.5°	256.1
25°	229.1
27.5°	202.1
30°	175.2
32.5°	148.7
35°	124.3
37.5°	103.3
40°	84.4
42.5°	66.9
45°	50.9
47.5°	38.4
50°	28.9
52.5°	21.5
55°	17.5
57.5°	15.5
60°	13.5
62.5°	12.0
65°	10.5
67.5°	9.0
70°	8.0
72.5°	6.5
75°	5.5
77.5°	4.5
80°	3.5
82.5°	2.5
85°	1.5
87.5°	0.5
90°	0.0

(END OF REPORT)