

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286360

Luminaire Tested: P3AS05R159030D2WDE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286360
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R159030D2WDE010 E3DLP1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 151.0 lumens
Efficiency: N/A
Efficacy: 13.6 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286360
CATALOG NUMBER: P3AS05R159030D2WDE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1286360
 CATALOG NUMBER: P3AS05R159030D2WDE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	86	86
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80	80
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	66	66	66
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62	62
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59	59	59	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	56	56	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	65104
5°	60180
10°	48051
15°	36300
20°	27629
25°	21050
30°	15091
35°	9851
40°	6040
45°	3659
50°	2422
55°	1873
60°	1623
65°	1401
70°	1282
75°	1271
80°	884
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3659 cd/sqm



TEST NUMBER: P1286360

CATALOG NUMBER: P3AS05R159030D2WDE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.2	16.0
10°-20°	44.7	29.6
20°-30°	39.8	26.3
30°-40°	23.5	15.6
40°-50°	9.7	6.4
50°-60°	4.5	3.0
60°-70°	2.8	1.8
70°-80°	1.5	1.0
80°-90°	0.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	108.7	72.0
0°-40°	132.2	87.6
0°-60°	146.4	97.0
0°-90°	151.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	151.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	297	
5°	273	24
15°	160	45
25°	87	40
35°	37	24
45°	12	10
55°	5	5
65°	3	3
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P1286360
CATALOG NUMBER: P3AS05R159030D2WDE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	296.9
1°	296.2
2°	294.0
3°	289.6
4°	282.2
5°	273.4
6°	263.8
7°	252.6
8°	240.8
9°	228.8
10°	215.8
12.5°	186.1
15°	159.9
17.5°	137.3
20°	118.4
22.5°	101.8
25°	87.0
27.5°	72.8
30°	59.6
32.5°	47.6
35°	36.8
37.5°	28.2
40°	21.1
42.5°	15.7
45°	11.8
47.5°	9.1
50°	7.1
52.5°	5.9
55°	4.9
57.5°	4.2
60°	3.7
62.5°	3.2
65°	2.7
67.5°	2.5
70°	2.0
72.5°	1.7
75°	1.5
77.5°	1.0
80°	0.7
82.5°	0.5
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)