

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287054

Luminaire Tested: P3AS13R159030D2WDE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287054
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R159030D2WDE010 E3DLP1WH
Description: 3in Adjustable Dim to Warm LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1117.1 lumens
Efficiency: N/A
Efficacy: 55.6 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287054
CATALOG NUMBER: P3AS13R159030D2WDE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1287054
 CATALOG NUMBER: P3AS13R159030D2WDE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	96	94	93	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	92	90	88	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	89	87	85	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	86	83	81	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	83	80	78	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	81	78	75	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	76	73	70	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	74	70	68	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	954222
5°	847015
10°	588210
15°	347857
20°	198117
25°	113257
30°	62668
35°	33408
40°	18492
45°	10017
50°	6243
55°	4932
60°	4254
65°	3891
70°	3462
75°	3643
80°	2778
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10017 cd/sqm



TEST NUMBER: P1287054

CATALOG NUMBER: P3AS13R159030D2WDE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	327.2	29.3
10°-20°	431.9	38.7
20°-30°	222.4	19.9
30°-40°	83.5	7.5
40°-50°	27.3	2.4
50°-60°	11.8	1.1
60°-70°	7.5	0.7
70°-80°	4.4	0.4
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	981.4	87.9
0°-40°	1064.9	95.3
0°-60°	1104.0	98.8
0°-90°	1117.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1117.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4352	
5°	3848	327
15°	1532	432
25°	468	222
35°	125	83
45°	32	27
55°	13	12
65°	8	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1287054
CATALOG NUMBER: P3AS13R159030D2WDE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4351.6
1°	4342.9
2°	4285.9
3°	4177.2
4°	4034.1
5°	3848.0
6°	3637.1
7°	3405.7
8°	3148.5
9°	2894.6
10°	2641.7
12.5°	2032.7
15°	1532.3
17.5°	1147.1
20°	849.0
22.5°	633.8
25°	468.1
27.5°	341.1
30°	247.5
32.5°	175.4
35°	124.8
37.5°	89.3
40°	64.6
42.5°	46.3
45°	32.3
47.5°	23.7
50°	18.3
52.5°	15.1
55°	12.9
57.5°	10.8
60°	9.7
62.5°	8.6
65°	7.5
67.5°	6.5
70°	5.4
72.5°	5.4
75°	4.3
77.5°	3.2
80°	2.2
82.5°	2.2
85°	1.1
87.5°	0.0
90°	0.0

(END OF REPORT)