

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286385

Luminaire Tested: P3AS05R209030D2WDE010 E3DLD1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1286385  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R209030D2WDE010 E3DLD1GPH  
Description: 3in Adjustable Dim to Warm LED luminaire with, R20 optic, 3000K CCT AND, 90CRI ,  
E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 192.9 lumens  
Efficiency: N/A  
Efficacy: 17.4 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1286385  
CATALOG NUMBER: P3AS05R209030D2WDE010 E3DLD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1286385

CATALOG NUMBER: P3AS05R209030D2WDE010 E3DLD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91				91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	90	87	85	83				83
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76				76
4	94	86	79	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70				70
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65				65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60				60
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55				55
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52				52
9	72	61	55	50	70	61	55	50	60	54	50	59	54	50	58	53	50	48				48
10	68	58	51	47	67	57	51	47	56	51	47	56	51	47	55	50	47	45				45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	47737
5°	46467
10°	42751
15°	37617
20°	32273
25°	27098
30°	21902
35°	16677
40°	11851
45°	7846
50°	4844
55°	3173
60°	2895
65°	2646
70°	2500
75°	2288
80°	2147
85°	1761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7846 cd/sqm



TEST NUMBER: P1286385

CATALOG NUMBER: P3AS05R209030D2WDE010 E3DLD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	19.5	10.1
10°-20°	46.1	23.9
20°-30°	51.2	26.5
30°-40°	39.1	20.2
40°-50°	20.0	10.4
50°-60°	8.2	4.2
60°-70°	5.1	2.6
70°-80°	2.9	1.5
80°-90°	0.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	116.9	60.6
0°-40°	155.9	80.8
0°-60°	184.1	95.4
0°-90°	192.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	192.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	218	
5°	211	20
15°	166	46
25°	112	51
35°	62	39
45°	25	20
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1286385  
CATALOG NUMBER: P3AS05R209030D2WDE010 E3DLD1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	217.7
1°	218.0
2°	217.0
3°	215.7
4°	213.8
5°	211.1
6°	207.9
7°	204.5
8°	200.8
9°	196.4
10°	192.0
12.5°	179.2
15°	165.7
17.5°	152.0
20°	138.3
22.5°	124.5
25°	112.0
27.5°	99.5
30°	86.5
32.5°	74.3
35°	62.3
37.5°	51.7
40°	41.4
42.5°	32.6
45°	25.3
47.5°	19.1
50°	14.2
52.5°	10.5
55°	8.3
57.5°	7.6
60°	6.6
62.5°	5.9
65°	5.1
67.5°	4.4
70°	3.9
72.5°	3.2
75°	2.7
77.5°	2.2
80°	1.7
82.5°	1.2
85°	0.7
87.5°	0.2
90°	0.0

(END OF REPORT)