

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287079

Luminaire Tested: P3AS13R209030D2WDE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287079
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R209030D2WDE010 E3DLD1WH
Description: 3in Adjustable Dim to Warm LED luminaire with, R20 optic, 3000K CCT AND, 90CRI ,
E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 848.0 lumens
Efficiency: N/A
Efficacy: 42.2 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287079
CATALOG NUMBER: P3AS13R209030D2WDE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1287079

CATALOG NUMBER: P3AS13R209030D2WDE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91				91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	90	87	85	83				83
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76				76
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70				70
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65				65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60				60
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55				55
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52				52
9	72	61	55	50	70	61	55	50	60	54	50	59	54	50	58	53	50	48				48
10	68	58	51	47	67	57	51	47	56	51	47	56	51	47	55	50	47	45				45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	209764
5°	204160
10°	187794
15°	165313
20°	141762
25°	119112
30°	96293
35°	73241
40°	52098
45°	34422
50°	21321
55°	13992
60°	12762
65°	11726
70°	11028
75°	9997
80°	9471
85°	8051

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 34422 cd/sqm



TEST NUMBER: P1287079

CATALOG NUMBER: P3AS13R209030D2WDE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.8	10.1
10°-20°	202.7	23.9
20°-30°	225.0	26.5
30°-40°	171.7	20.2
40°-50°	87.9	10.4
50°-60°	36.1	4.3
60°-70°	22.5	2.7
70°-80°	12.6	1.5
80°-90°	3.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	513.5	60.6
0°-40°	685.2	80.8
0°-60°	809.2	95.4
0°-90°	848.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	848.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	957	
5°	928	86
15°	728	203
25°	492	225
35°	274	172
45°	111	88
55°	37	36
65°	23	23
75°	12	13
85°	3	4
90°	0	



TEST NUMBER: P1287079
CATALOG NUMBER: P3AS13R209030D2WDE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	956.6
1°	957.6
2°	953.3
3°	947.9
4°	939.3
5°	927.5
6°	913.5
7°	898.4
8°	882.2
9°	862.8
10°	843.4
12.5°	787.4
15°	728.2
17.5°	667.9
20°	607.5
22.5°	547.2
25°	492.3
27.5°	437.3
30°	380.3
32.5°	326.4
35°	273.6
37.5°	227.3
40°	182.0
42.5°	143.3
45°	111.0
47.5°	84.0
50°	62.5
52.5°	46.3
55°	36.6
57.5°	33.4
60°	29.1
62.5°	25.9
65°	22.6
67.5°	19.4
70°	17.2
72.5°	14.0
75°	11.8
77.5°	9.7
80°	7.5
82.5°	5.4
85°	3.2
87.5°	1.1
90°	0.0

(END OF REPORT)