

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287096

Luminaire Tested: P3AS13R259030D2WDE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287096
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R259030D2WDE010 E3DL1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 552.0 lumens
Efficiency: N/A
Efficacy: 27.5 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287096

CATALOG NUMBER: P3AS13R259030D2WDE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1287096

CATALOG NUMBER: P3AS13R259030D2WDE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91
4	101	95	90	87	99	94	89	86	92	88	85		90	87	84		88
5	97	90	85	82	96	89	85	81	88	84	81		86	83	80		85
6	94	86	81	78	92	86	81	78	84	80	77		83	79	77		82
7	90	83	78	74	89	82	77	74	81	77	74		80	76	73		79
8	87	79	74	71	86	79	74	71	78	74	71		77	73	70		76
9	84	76	71	68	83	76	71	68	75	71	68		74	70	68		73
10	81	73	69	65	80	73	68	65	72	68	65		72	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	354094
5°	330354
10°	264635
15°	179638
20°	108696
25°	63560
30°	36208
35°	19916
40°	10563
45°	5551
50°	3241
55°	2409
60°	2061
65°	2179
70°	2052
75°	1779
80°	1389
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5551 cd/sqm

TEST NUMBER: P1287096

CATALOG NUMBER: P3AS13R259030D2WDE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.2	24.1
10°-20°	217.5	39.4
20°-30°	124.3	22.5
30°-40°	49.1	8.9
40°-50°	15.0	2.7
50°-60°	5.9	1.1
60°-70°	4.0	0.7
70°-80°	2.2	0.4
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	475.1	86.1
0°-40°	524.1	94.9
0°-60°	545.1	98.7
0°-90°	552.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	552.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1615	
5°	1501	133
15°	791	218
25°	263	124
35°	74	49
45°	18	15
55°	6	6
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1287096

CATALOG NUMBER: P3AS13R259030D2WDE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1614.8
1°	1611.6
2°	1598.4
3°	1575.2
4°	1543.0
5°	1500.8
6°	1451.2
7°	1395.3
8°	1330.4
9°	1264.0
10°	1188.5
11°	1114.1
12°	1032.4
13°	951.7
14°	868.8
15°	791.3
17.5°	613.5
20°	465.8
22.5°	349.8
25°	262.7
27.5°	194.7
30°	143.0
32.5°	103.4
35°	74.4
37.5°	52.8
40°	36.9
42.5°	25.3
45°	17.9
47.5°	12.7
50°	9.5
52.5°	7.4
55°	6.3
57.5°	5.8
60°	4.7
62.5°	4.2
65°	4.2
67.5°	3.7
70°	3.2
72.5°	2.6
75°	2.1
77.5°	1.6
80°	1.1
82.5°	1.1
85°	0.5
87.5°	0.5



TEST NUMBER: P1287096

CATALOG NUMBER: P3AS13R259030D2WDE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)