

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286414

Luminaire Tested: P3AS05R259030D2WDE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286414
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R259030D2WDE010 E3DLD1LI
Description: 3in Adjustable Dim to Warm LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,
E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 401.0 lumens
Efficiency: N/A
Efficacy: 36.1 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286414

CATALOG NUMBER: P3AS05R259030D2WDE010 E3DLD1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1286414

CATALOG NUMBER: P3AS05R259030D2WDE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	95299
5°	93022
10°	86215
15°	76777
20°	65992
25°	56084
30°	46159
35°	35978
40°	25877
45°	16436
50°	9722
55°	6690
60°	6140
65°	5707
70°	5129
75°	4660
80°	4420
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16436 cd/sqm

TEST NUMBER: P1286414

CATALOG NUMBER: P3AS05R259030D2WDE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.2	9.8
10°-20°	93.9	23.4
20°-30°	106.1	26.5
30°-40°	83.9	20.9
40°-50°	42.4	10.6
50°-60°	17.0	4.2
60°-70°	10.9	2.7
70°-80°	6.0	1.5
80°-90°	1.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	239.2	59.6
0°-40°	323.1	80.6
0°-60°	382.5	95.4
0°-90°	401.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	401.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	435	
5°	423	39
15°	338	94
25°	232	106
35°	134	84
45°	53	42
55°	18	17
65°	11	11
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1286414

CATALOG NUMBER: P3AS05R259030D2WDE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	434.6
1°	434.6
2°	433.1
3°	430.6
4°	427.1
5°	422.6
6°	417.1
7°	410.6
8°	403.6
9°	395.7
10°	387.2
11°	377.7
12°	368.7
13°	358.2
14°	348.2
15°	338.2
17.5°	310.2
20°	282.8
22.5°	256.8
25°	231.8
27.5°	207.3
30°	182.3
32.5°	158.9
35°	134.4
37.5°	111.9
40°	90.4
42.5°	70.4
45°	53.0
47.5°	39.5
50°	28.5
52.5°	21.5
55°	17.5
57.5°	16.0
60°	14.0
62.5°	12.5
65°	11.0
67.5°	9.5
70°	8.0
72.5°	7.0
75°	5.5
77.5°	4.5
80°	3.5
82.5°	2.5
85°	1.5
87.5°	0.5



TEST NUMBER: P1286414

CATALOG NUMBER: P3AS05R259030D2WDE010 E3DLD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)